



### Specifications

- Housing material: cold-rolled steel
- Housing finish: black powder coat
- AC voltage: 120V or 250V
- Current rating: 15A, 20A, 30A or 60A
- Outlets: NEMA 5-15R or 5-20R or IEC C-13 or C-19
- Input plug cord: 10' cable with NEMA plug, IEC 320 C-20 inlet, or 60A IEC 309 plug
- Surge protection:
  - Protection modes: L-N, L-G, N-G
  - Joule rating: 720

### Power Strips, Vertical Mount

Includes: (1) strip, (1) kit mounting hardware, universal mounting brackets

Electrical Specification	Receptacle Type	Outlets Front	Plug Type	No. of Circuits	Surge Protected	Switch	Current Monitor	Catalog No.
15A-120V	NEMA 5-15R	10	NEMA 5-15P	1	No	No	No	<b>PR104</b>
20A-120V	NEMA 5-20R	10	NEMA 5-20P	1	No	No	No	<b>PR10420</b>
15A-120V	NEMA 5-15R	20	NEMA 5-15P	1	No	No	No	<b>PR206</b>
20A-120V	NEMA 5-20R	20	NEMA 5-20P	1	No	No	No	<b>PR20620</b>
20A-120V	NEMA 5-20R	20	NEMA 5-20P	1	No	No	No	<b>PR20620TL<sup>1</sup></b>
20A-120V	NEMA 5-20R	20	NEMA 5-20P	1	No	Yes	Yes	<b>PR20820DRTL<sup>2</sup></b>
30A-120V	NEMA 5-20R	20	NEMA L5-30P	1	No	No	No	<b>PR20830</b>
20/16A/circuit 120V	NEMA 5-20R	20	NEMA 5-20P	2	No	No	No	<b>PR20820A<sup>3</sup></b>
20/16A-120/250V	IEC 320C-13	20	IEC 320 C20	1	No	No	No	<b>PR20820I<sup>4</sup></b>
30/24A-250V	IEC 320C-13	24	NEMA L6-30P	1	No	No	No	<b>PR24</b>

<sup>1</sup>PR20620TL includes a Twist-Lock® plug.

<sup>2</sup>PR20820DRTL features a digital current meter and a 20A Twist-Lock® plug.

<sup>3</sup>PR20820A features (2) 20A circuits each fed by 10' cable with NEMA 5-20 plug.

<sup>4</sup>PR20820I includes an IEC 320 (C-20) inlet for power input.

### Mounting Brackets for Vertical Power Strips

Description	Catalog No.
L-brackets: turned in for rack/rail mounting; turned out to extend mounting options an additional 8 inches	<b>PRSLB4</b>
For left, right, front or back rail mounting; may be installed in conjunction with other equipment mounted in the same "U" space	<b>PREZB</b>