



MCCPSS19TS



HPWPWR



PR10720

Specifications

- Housing material: cold-rolled steel
- Housing finish: black powder coat
- AC voltage: 120V or 250V
- Current rating: 15A, 20A, 30A or 60A
- Outlets: NEMA 5-15R or 5-20R or IEC C-13 or C-19
- Input plug cord: 10' cable with NEMA plug, IEC 320 C-20 inlet, or 60A IEC 309 plug
- Surge protection:
 - Protection modes: L-N, L-G, N-G
 - Joule rating: 720

Power Strips, Horizontal

Includes: (1) strip, (1) kit mounting hardware

| Electrical Specification | Receptacle Type | Outlets | | Mounting Style | Surge Protected | Transformer Spaced | Switch | Current Monitor | Catalog No. |
|--------------------------|-----------------|---------|------|----------------|-----------------|--------------------|-----------|-----------------|----------------------------|
| | | Front | Rear | | | | | | |
| 15A-120V | NEMA 5-15R | 0 | 10 | Flush | No | No | Yes | No | HPWPWR |
| 15A-120V | NEMA 5-15R | 0 | 10 | Flush | Yes | No | Yes | No | MCCPSS19 |
| 15A-120V | NEMA 5-15R | 4 | 4 | Recess | Yes | Yes | No | No | MCCPSS19TS |
| 20A-120V | NEMA 5-20R | 0 | 10 | Flush | No | No | No | No | PR10120 |
| 20/16A, 120/250V | IEC 320C-13 | 10 | 0 | Flush | No | No | No | No | PR10720¹ |
| 15A-120V | NEMA 5-15R | 0 | 6 | Flush | No | No | No | No | PR0615 |
| 20A-120V | NEMA 5-20R | 0 | 10 | Flush | No | No | Yes | Yes | PR1020 |
| 60A-250V | IEC 320C-19 | 0 | 3 | Adjustable | No | N/A | CB/Switch | No | PR0360² |

¹PR10720 includes an IEC 320 (C-20) inlet for power input. Vertical mount brackets are also included.

²PR0360 features 10' cable with IEC 60A 2P/3W plug.

Mounting Brackets for Horizontal Power Strips

| Description | Catalog No. |
|--|--------------|
| Adjustable mount brackets; allows numerous recess or flush mount options | PRAMB |
| Panel mount brackets; ideal for zero "U" mounting applications; effectively allows the unit to be hung from a cross beam or flat surface | PRPMB |

| Type | Catalog No. | Integral Fixed Brackets | Pre-Assembled Brackets Included | Optional Brackets Available |
|----------------|-------------|-------------------------|---------------------------------|-----------------------------|
| 19" Rack Mount | HPWPWR | Flush Mount | N/A | N/A |
| | MCCPSS19 | | | |
| | PR10120 | | | |
| | PR0615 | | | |
| | PR1020 | | | |
| | MCCPSS19TS | N/A | Recess Mount | PRAMB PRPMB |
| | PR10720 | N/A | Flush Mount and PRSLB4 | PREZB |
| | PR0360 | N/A | PRAMB | PRPMB |