

	1-Gang			2-Gang		
	Description	Color	1-Gang	Description	Color	2-Gang
1-Gang Specialty Boxes	Low Profile Switch/Receptacle Base has ½" trade size KOs.	Ivory White	HBL5748SIV HBL5748SW A: 4.54" (115.32) B: 2.82" (71.63) C: 1.13" (28.70)	Alarm Device Box Surface mounting of alarm devices and safety signals.	Ivory Red	HBL5752IV HBL5752R A: 4.54" (115.32) B: 4.64" (117.86) C: 1.38" (35.05)
	Combination Switch/Recept. Connects surface runs of ½" trade size conduit, one raceway twistout each side and three raceway twistouts top and bottom.	Ivory White	HBL5745IV HBL5745W A: 4.54" (115.32) B: 2.82" (71.63) C: 1.75" (44.45)	Extra Deep Alarm Device Box For surface mounting of alarm devices and safety signals. Cover is 2.75" (69.85) deep.	Ivory Red	HBL5753IV HBL5753R A: 4.54" (115.32) B: 4.64" (117.86) C: 2.75" (69.85)
	Utility Box* For use as a tee, cross, pull box, junction box or blank box. Base has ½" trade size KOs.	Ivory	HBL57242IV HBL57242W A: 4.12" (104.78) B: 2.00" (50.80) C: 1.39" (35.31)	Distribution Box Twistouts permit three parallel raceway runs on each side. Cover takes devices with mounting screw centers of 2.75" (69.85), 3.5" (89.00), 4.0625" (103.00) and canopy fixture not larger than 4.625" (117.00). Can be used with HBL5736IV (blank cover) to create junction box.	Ivory	HBL5735IV A: 4.54" (115.32) B: 4.64" (117.86) C: 1.38" (35.05)

Note: *Use catalog number HBL5791 for connecting ½ in. EMT to HBL5745 and HBL57242 boxes.



	Description	Color	Round Boxes		
			4.75 inches O.D.	5.50 inches O.D.	6.38 inches O.D.
Round Boxes	Extension Box (Open Base) For mounting on 3.25" (83.00) or 4" (102.00) round or square conduit boxes or other recessed outlets. Cover takes any device with mounting screw centers of 2.75" (69.85), 3.5" (89.00) and 4.06" (103.00).	Ivory White	HBL5737IV HBL5737W A: 1.02" (26.00) B: 4.75" (120.65)	HBL5737AIV HBL5737AW A: 1.02" (26.00) B: 5.50" (140.00)	HBL5739AIV — A: 1.02" (26.00) B: 6.38" (162.01)
	Fixture Box (Solid Base) To hang fixtures. Cover takes any device with mounting screw centers of 2.75" (69.85), 3.5" (89.00) and 4.06" (103.00). Both boxes can be used as a pull or junction box when used with HBL5736IV (blank cover).	Ivory White	HBL5738IV HBL5738W A: 1.02" (26.00) B: 4.75" (120.65)	HBL5738AIV HBL5738AW A: 1.02" (26.00) B: 5.50" (140.00)	HBL5739IV HBL5739W A: 1.02" (26.00) B: 6.38" (162.01)

	Specialty Round Boxes			Round Covers		
	Description	Color	Catalog Number	Description	Color	Catalog Number
Specialty Round Boxes	Outlet Box For devices with mounting screw centers of 1.47" (37.00), 1.63" (41.00), 1.69" (44.00) or 1.84" (46.00).	Ivory	HBL5733IV A: 1.02" (26.00) B: 3.00" (76.00)	Blank Cover For use with HBL5733IV. Has ½" trade size KO in center.	Ivory	HBL5731IV A: .24" (6.10) B: 2.40" (60.96)
	Fanbox with Solid Base Cover accepts fan bracket with mounting centers of 3.2" (81.00). Rated for fans and fixtures up to 50 lbs.	Ivory White	HBL5738AFIV HBL5738AFW A: .38" (9.75) B: 4.19" (106.30)	Blank Cover For use with HBL5735IV, HBL5737IV/W, HBL5737AIV/W, HBL5739AIV, HBL5738IV/W, HBL5738AIV/W and HBL5739IV/W. Has ½" trade size KO in center.	Ivory White	HBL5736IV HBL5736W A: .38" (9.75) B: 4.19" (106.30)
	Retrofit Box for Fire Alarm Detectors For installing round alarm sensors.	Ivory White	HBL5739AABIV HBL5739AABW A: 1.62" (41.15) B: 6.50" (165.10)			

Dimensions in Inches (mm)