

HBL4750 Series	Description	Color	Catalog Number	Description	Color	Catalog Number
	Single Channel Base Packed 50 ft. (15.24m) per carton, 10 ft. (3m) lengths. Assembled cover and base dimensions. W: 4.75" (120.65) H: 1.75" (44.45)	Ivory Gray	HBL4750B10IV HBL4750B10GY A: 120.00" (3048.00) B: 4.75" (120.65) C: 1.62" (41.20)	5 Ft. Cover Packed 50 ft. (15.24m) per carton, 5 ft. (1.5m) lengths. 31.5 In. Precut Cover* For 36 in. (915.00) centers with HBL4747 and HBL4750 Plates. 19.5 In. Precut Cover* For 24 in. (610.00) centers with HBL4747 and HBL4750 Plates. 13.5 In. Precut Cover* For 18 in. (457.00) centers with HBL4747 and HBL4750 Plates. 7.5 In. Precut Cover* For 12 in. (305.00) centers with HBL4747 and HBL4750 Plates.	Ivory Gray Ivory Gray Ivory Gray Ivory Gray	HBL4750CIV HBL4750CGY A: 60.00" (1,524.0) B: 4.75" (120.65) HBL4750C315IV HBL4750C315GY A: 31.50" (800.10) B: 4.75" (120.65) HBL4750C195IV HBL4750C195GY A: 19.50" (495.30) B: 4.75" (120.65) HBL4750C135IV HBL4750C135GY A: 13.50" (342.90) B: 4.75" (120.65) HBL4750C075IV HBL4750C075GY A: 7.50" (190.50) B: 4.75" (120.65)

Note: *Packed 10 pieces per carton. Device centers vary based on cover selection. Consult factory for details.

Fittings	Description	Color	Catalog Number	Description	Color	Catalog Number
	Divider Divides HBL4750 Raceway into two channels. Packed 50 ft. (15.24m) per carton, 5 ft. (1.5m) lengths. HBL4751DA Divider Clips are required to hold divider in place.	Painted Steel	HBL4750DGY A: 60.00" (1,524.0) B: 1.51" (38.46)	By-Pass Divider Divides HBL4750 Raceway into two channels with a 70/30 split. Allows for a larger power or datacom wire fill. HBL4751DA Divider Clips are required to hold divider in place.	Painted Steel	HBL4750BP A: 7.12" (180.74) B: .89" (22.54)
	Divider Clip Required for holding HBL4750DGY in place. Use one every 2.5 ft. (.762m).	Steel**	HBL4751DA A: 4.64" (117.77) B: 1.46" (37.07)	Wire Clip (Plated) For holding conductors in place.	Steel**	HBL4750WCGY A: 4.60" (116.74) B: 1.58" (40.13) C: 1.00" (25.40)
	Internal Corner Coupling (Plated) Concealed fitting for making an internal corner while continuing original run in a straight line.	Steel**	HBL4717TCAGY A: 4.59" (116.59) B: 2.71" (68.73) C: 1.47" (37.34)	Coupling (Plated) For joining lengths of HBL4750 Raceway. Sold in pairs.	Steel**	HBL4751AC A: 1.47" (37.30) B: .42" (10.59)

Note: **Galvanized Steel.