

## Hubbell SystemOne 10-Gang Floor Boxes



### CFB10G55 Series – Rectangular Covers for 5 ½ in. Minimum Pour

- Designed for applications requiring up to 2 in. conduits (integrated 2 in. knockouts) and a rectangular cover
- When a 5 ½ in. concrete pour is required the insert is removed and requires the finished floor type to be carpet or another engineered floor type

Includes:

- A ½ in. plastic cover insert is included and allows for easy use in tile, finished concrete or other mediums



Catalog Number	Box Type	Min.Pour Depth	Plate Depth	Device Volume	Cover Series	Knockouts
<b>CFB10G55</b>	Standard	5 ½ in.	2 ½ in.	33 cu. in./	610G	¾ in. to 2 in.
<b>CFB10G55CR</b>	On-grade			89 cu. in		

### CFB10G55R Series – Round Covers for 6 ¼ in. Minimum Pour

- Designed for applications requiring up to 2 in. conduits (integrated 2 in. knockouts) and a round cover
- Minimum concrete pour of 6 ¼ in. and includes a collar for post pour adjustment of ¼ in.
- Suitable for all floor finish types

Catalog Number	Box Type	Min.Pour Depth	Plate Depth	Device Volume	Cover Series	Knockouts
<b>CFB10G55R</b>	Standard	6 ¼ in.	2 ½ in.	33 cu. in./	CFBS1R8	¾ in. to 2 in.
<b>CFB10G55RCR</b>	On-grade			89 cu. in		

### Plate Layout - NEC® Required Volume

<b>CFB10NEMA46</b>	148 cu. in.				
<b>CFB10NEMA</b>	25 cu. in.	68 cu. in.		80 cu. in.	
<b>Standard layout</b>	25 cu. in.	48 cu. in.		71 cu. in.	
	1	2	3	4	5
<b>Standard layout</b>	25 cu. in.	48 cu. in.		71 cu. in.	
<b>CFB10NEMA</b>		68 cu. in.		80 cu. in.	
<b>FB10MPNEMA4G</b>	148 cu. in.				



CFB10NEMA



FB10MPNEMA4G