

IMPORTANT

Read all breaking strength, safety and technical data relating to this product. Pages V-41 to V-45.

Light Duty, Single Eye, Closed Mesh, Single Weave

For permanent support when cable end is available to be installed.



| Cable Diameter Range Inches (cm) | Approx. Breaking Strength Lbs. (N) | | E Inches (cm) | M Inches (cm) | Tin-Coated Bronze | Stainless Steel |
|-------------------------------------|------------------------------------|-----------------|------------------|------------------|----------------------|-----------------|
| | Tin-Coated Bronze | Stainless Steel | | | | |
| .23"-.31" (.58-.79) | 290 (1,290) | 700 (3,114) | 3" (7.62) | 3.75" (9.52) | 02216001 | 02416001 |
| .29"-.37" (.74-.94) | 290 (1,290) | 700 (3,114) | 5" (12.70) | 4.25" (10.79) | 02216002 | 02416002 |
| .35"-.44" (.89-1.12) | 500 (2,224) | 850 (3,781) | 5.5" (13.97) | 4.75" (12.06) | 02216003 | 02416003 |
| .41"-.50" (1.04-1.27) | 500 (2,224) | 850 (3,781) | 5.5" (13.97) | 5" (12.70) | 02216004 | 02416004 |
| .46"-.56" (1.17-1.42) | 660 (2,936) | 850 (3,781) | 6" (15.24) | 5.25" (13.33) | 02216005 | 02416005 |
| .52"-.62" (1.32-1.57) | 790 (3,514) | 1,050 (4,670) | 7" (17.78) | 6.25" (15.87) | 02216006 | 02416006 |
| .58"-.68" (1.47-1.73) | 790 (3,514) | 1,050 (4,670) | 7" (17.78) | 6" (15.24) | 02216007 | 02416007 |
| .64"-.75" (1.63-1.90) | 790 (3,514) | 1,050 (4,670) | 7" (17.78) | 6.75" (17.14) | 02216008 | 02416008 |
| .70"-.81" (1.78-2.06) | 790 (3,514) | 2,050 (9,119) | 7" (17.78) | 7.25" (18.41) | 02216009 | 02416009 |
| .75"-.87" (1.90-2.21) | 1,020 (4,537) | 2,050 (9,119) | 8" (20.32) | 8" (20.32) | 02216010 | 02416010 |
| .81"-.94" (2.06-2.39) | 1,020 (4,537) | 2,050 (9,119) | 8" (20.32) | 8.25" (20.95) | 02216011 | 02416011 |
| .87"-1.00" (2.21-2.54) | 1,020 (4,537) | — | 8" (20.32) | 8.75" (22.22) | 02216012 | — |
| .94"-1.06" (2.39-2.69) | 1,020 (4,537) | 2,050 (9,119) | 9" (22.86) | 9" (22.86) | 02216013 | 02416013 |
| 1.00"-1.18" (2.54-3.00) | 1,020 (4,537) | 2,050 (9,119) | 9" (22.86) | 9.5" (24.13) | 02216014 | 02416014 |
| 1.06"-1.25" (2.69-3.17) | 1,020 (4,537) | 2,050 (9,119) | 9" (22.86) | 9.5" (24.13) | 02216015 | 02416015 |

Heavy Duty, Single Eye, Closed Mesh, Multi-Weave

For permanent support when cable end is available to be installed.



| Cable Diameter Range Inches (cm) | Approx. Breaking Strength Lbs. (N) | | E Inches (cm) | M Inches (cm) | Tin-Coated Bronze | Stainless Steel |
|-------------------------------------|------------------------------------|-----------------|------------------|------------------|----------------------|-----------------|
| | Tin-Coated Bronze | Stainless Steel | | | | |
| .23"-.31" (.58-.79) | 500 (2,224) | 1,400 (6,228) | 5" (12.70) | 4.5" (11.43) | 02217001 | 02417001 |
| .29"-.37" (.74-.94) | 500 (2,224) | 1,150 (5,115) | 5" (12.70) | 5.5" (13.97) | 02217002 | 02417002 |
| .35"-.44" (.89-1.12) | 870 (3,870) | 1,700 (7,562) | 6" (15.24) | 6.5" (16.51) | 02217003 | 02417003 |
| .41"-.50" (1.04-1.27) | 870 (3,870) | 1,700 (7,562) | 6" (15.24) | 7.5" (19.05) | 02217004 | 02417004 |
| .46"-.56" (1.17-1.42) | 1,050 (4,670) | 2,100 (9,341) | 6" (15.24) | 8" (20.32) | 02217005 | 02417005 |
| .52"-.62" (1.32-1.57) | 1,050 (4,670) | 2,100 (9,341) | 7" (17.78) | 8.5" (21.59) | 02217006 | 02417006 |
| .58"-.68" (1.47-1.73) | 1,050 (4,670) | 2,100 (9,341) | 7" (17.78) | 9.5" (24.13) | 02217007 | 02417007 |
| .64"-.75" (1.63-1.90) | 1,390 (6,183) | 4,161 (18,509) | 7" (17.78) | 9.5" (24.13) | 02217008 | 02417008 |
| .70"-.81" (1.78-2.06) | 1,390 (6,183) | 4,100 (18,238) | 8" (20.32) | 10.5" (26.67) | 02217009 | 02417009 |
| .75"-.87" (1.90-2.21) | 1,390 (6,183) | — | 8" (20.32) | 10.5" (26.67) | 02217010 | — |
| .81"-.94" (2.06-2.39) | 1,390 (6,183) | — | 8" (20.32) | 10.5" (26.67) | 02217011 | — |
| .87"-1.00" (2.21-2.54) | 1,790 (7,962) | 5,350 (23,798) | 8" (20.32) | 11.5" (29.21) | 02217012 | 02417012 |
| .94"-1.06" (2.39-2.69) | 1,790 (7,962) | 5,300 (23,576) | 9" (22.86) | 12.5" (31.75) | 02217013 | 02417013 |
| 1.00"-1.18" (2.54-3.00) | 1,790 (7,962) | 5,300 (23,576) | 9" (22.86) | 13.5" (34.29) | 02217014 | 02417014 |
| 1.06"-1.25" (2.69-3.17) | 1,790 (7,962) | 5,350 (23,798) | 9" (22.86) | 14.5" (36.83) | 02217015 | 02417015 |

Note: E-Eye length. M-Mesh length at nominal diameter.

Screw Hook
Catalog Number **20303001**
Yield Strength 900 lbs (4003 N)

