

**IMPORTANT**

Read all breaking strength, safety and technical data relating to this product. Pages V-41 to V-45.

**Light Duty, Universal Eye, Closed Mesh, Single Weave**

For permanent support when cable end is available to be installed.

Cable Diameter Range Inches (cm)	Approx. Breaking Strength Lbs. (N)	E Inches (cm)	M Inches (cm)	Catalog Number
.23"-.31" (.58-.79)	290 (1,290)	9" (22.86)	3.75" (9.52)	<b>02216016</b>
.29"-.37" (.74-.94)	290 (1,290)	10" (25.40)	4.25" (10.79)	<b>02216017</b>
.35"-.44" (.89-1.12)	500 (2,224)	10" (25.40)	4.75" (12.06)	<b>02216018</b>
.41"-.50" (1.04-1.27)	500 (2,224)	11" (27.94)	5" (12.70)	<b>02216019</b>
.46"-.56" (1.17-1.42)	660 (2,936)	12" (30.48)	5.25" (13.33)	<b>02216020</b>
.52"-.62" (1.32-1.57)	790 (3,514)	13" (33.02)	6.25" (15.87)	<b>02216021</b>
.58"-.68" (1.47-1.73)	790 (3,514)	13" (33.02)	6.5" (16.51)	<b>02216022</b>
.64"-.75" (1.63-1.90)	790 (3,514)	13" (33.02)	6.75" (17.14)	<b>02216023</b>
.70"-.81" (1.78-2.06)	790 (3,514)	13" (33.02)	7.25" (18.41)	<b>02216024</b>
.75"-.87" (1.90-2.21)	1,020 (4,537)	14" (35.56)	8" (20.32)	<b>02216025</b>
.81"-.94" (2.06-2.39)	1,020 (4,537)	14" (35.56)	8.25" (20.95)	<b>02216026</b>
.87"-1.00" (2.21-2.54)	1,020 (4,537)	14" (35.56)	8.75" (22.22)	<b>02216027</b>
.94"-1.06" (2.39-2.69)	1,020 (4,537)	15" (38.10)	9" (22.86)	<b>02216028</b>
1.00"-1.18" (2.54-3.00)	1,020 (4,537)	15" (38.10)	9.5" (24.13)	<b>02216029</b>
1.06"-1.25" (2.69-3.17)	1,020 (4,537)	15" (38.10)	9.5" (24.13)	<b>02216030</b>



**Heavy Duty, Universal Eye, Closed Mesh, Multi-Weave**

For permanent support when cable end is available to be installed.

Cable Diameter Range Inches (cm)	Approx. Breaking Strength Lbs. (N)	E Inches (cm)	M Inches (cm)	Catalog Number
.23"-.31" (.58-.79)	500 (2,224)	11" (27.94)	4.5" (11.43)	<b>02217016</b>
.28"-.37" (.74-.94)	500 (2,224)	11" (27.94)	5.5" (13.97)	<b>02217017</b>
.35"-.44" (.89-1.12)	870 (3,870)	12" (30.48)	6.5" (16.51)	<b>02217018</b>
.41"-.50" (1.04-1.27)	870 (3,870)	12" (30.48)	7.5" (19.05)	<b>02217019</b>
.46"-.56" (1.17-1.42)	1,050 (4,670)	12" (30.48)	8" (20.32)	<b>02217020</b>
.52"-.62" (1.32-1.57)	1,050 (4,670)	13" (33.02)	8.5" (21.59)	<b>02217021</b>
.58"-.68" (1.47-1.73)	1,050 (4,670)	13" (33.02)	9.5" (24.13)	<b>02217022</b>
.64"-.75" (1.63-1.90)	1,390 (6,183)	13" (33.02)	9.5" (24.13)	<b>02217023</b>
.70"-.81" (1.78-2.06)	1,390 (6,183)	14" (35.56)	10.5" (26.67)	<b>02217024</b>
.75"-.87" (1.90-2.21)	1,390 (6,183)	14" (35.56)	10.5" (26.67)	<b>02217025</b>
.81"-.94" (2.06-2.39)	1,390 (6,183)	14" (35.56)	10.5" (26.67)	<b>02217026</b>
.87"-1.00" (2.21-2.54)	1,790 (7,962)	14" (35.56)	11.5" (29.21)	<b>02217027</b>
.94"-1.06" (2.39-2.69)	1,790 (7,962)	15" (38.10)	12.5" (31.75)	<b>02217028</b>
1.00"-1.18" (2.54-3.00)	1,790 (7,962)	15" (38.10)	13.5" (34.29)	<b>02217029</b>
1.06"-1.25" (2.69-3.17)	1,790 (7,962)	15" (38.10)	14.5" (36.83)	<b>02217030</b>



Note: E-Eye length. M-Mesh length at nominal diameter.