

**Benefits**

- Helps prevent conduit pull-out and damage at the fitting.
- Reduces equipment downtime.

**IMPORTANT**

Read all breaking strength, safety and technical data relating to this product. Pages V-74 to V-76.

**Straight With Male Fitting**

Conduit Trade Size Inches	NPT Fitting Size Inches	Mesh Length Inches (cm)	Catalog Number (Insulated)	Catalog Number (Non-insulated)
3/8	1/2	3" (7.62)	<b>074093511</b>	<b>074093401</b>
1/2	1/2	3.5" (8.89)	<b>074093512</b>	<b>074093402</b>
3/4	3/4	4" (10.16)	<b>074093513</b>	<b>074093403</b>
1	1	5" (12.70)	<b>074093514</b>	<b>074093404</b>
1 1/4	1 1/4	6" (15.24)	<b>074093515</b>	<b>074093405</b>
1 1/2	1 1/2	6.75" (17.14)	<b>074093516</b>	<b>074093406</b>
2	2	8" (20.32)	<b>074093518</b>	<b>074093408</b>
2 1/2	2 1/2	9.75" (24.76)	<b>074093520</b>	<b>074093410</b>
3	3	11" (27.94)	<b>074093522</b>	<b>074093412</b>
4	4	14" (35.56)	<b>074093526</b>	—

**90° Angle With Male Fitting**

Conduit Trade Size Inches	NPT Fitting Size Inches	Mesh Length Inches (cm)	Catalog Number (Insulated)	Catalog Number (Non-insulated)
3/8	1/2	3" (7.62)	<b>074093541</b>	<b>074093421</b>
1/2	1/2	3.5" (8.89)	<b>074093542</b>	<b>074093422</b>
3/4	3/4	4" (10.16)	<b>074093543</b>	<b>074093423</b>
1	1	5" (12.70)	<b>074093544</b>	<b>074093424</b>
1 1/4	1 1/4	6" (15.24)	<b>074093545</b>	<b>074093425</b>
1 1/2	1 1/2	6.75" (17.14)	<b>074093546</b>	<b>074093426</b>
2	2	8" (20.32)	<b>074093548</b>	<b>074093428</b>
2 1/2	2 1/2	9.75" (24.76)	<b>074093550</b>	—
3	3	11" (27.94)	<b>074093552</b>	—

Note: For use with Liquidtight Metal conduit and PolyTuff® I Non-Metallic conduit.