

**IMPORTANT**  
 Read all breaking strength, safety and technical data relating to this product.  
 Page V-76



**Straight Male Hubbell Fitting**

| Conduit Trade Size Inches | NPT Fitting Size Inches | Mesh Length Inches (cm) | Catalog Number |
|---------------------------|-------------------------|-------------------------|----------------|
| 3/8                       | 1/2                     | 3.75" (9.52)            | <b>H038CNK</b> |
| 1/2                       | 1/2                     | 4.5" (11.43)            | <b>H050CNK</b> |
| 3/4                       | 3/4                     | 6.25" (15.87)           | <b>H075CNK</b> |
| 1                         | 1                       | 7.5" (19.05)            | <b>H100CNK</b> |
| 1 1/4                     | 1 1/4                   | 9" (22.86)              | <b>H125CNK</b> |
| 1 1/2                     | 1 1/2                   | 13.5" (34.29)           | <b>H150CNK</b> |
| 2                         | 2                       | 14.5" (36.83)           | <b>H200CNK</b> |



**90° Male Hubbell Fitting**

| Conduit Trade Size Inches | NPT Fitting Size Inches | Mesh Length Inches (cm) | Catalog Number  |
|---------------------------|-------------------------|-------------------------|-----------------|
| 3/8                       | 1/2                     | 3.75" (9.52)            | <b>H0389CNK</b> |
| 1/2                       | 1/2                     | 4.5" (11.43)            | <b>H0509CNK</b> |
| 3/4                       | 3/4                     | 6.25" (15.87)           | <b>H0759CNK</b> |
| 1                         | 1                       | 7.5" (19.05)            | <b>H1009CNK</b> |
| 1 1/4                     | 1 1/4                   | 9" (22.86)              | <b>H1259CNK</b> |
| 1 1/2                     | 1 1/2                   | 13.5" (34.29)           | <b>H1509CNK</b> |
| 2                         | 2                       | 14.5" (36.83)           | <b>H2009CNK</b> |