

Features

- Low profile, less than 1 inch deep
- Self-grounding feature is standard
- Operating temperature: -20°C to 60°C
- UL Listed E3896, CSA Certified

Combination Quiet Rocker Switches/Devices



RCD111W




RCD101W




RCD108W



RCD109W

Description	Three (3) Single Pole Switches	Two (2) Single Pole Switches	Single Pole and Three Way Switch	 * Single Pole Switch, Tamper-Resistant, 2 Pole, 3 Wire, Receptacle	Single Pole Switch, 2 Pole, 3 Wire Receptacle
	Termination	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire
Rating	15A 120-277V AC	15A 120-277V AC	15A 120-277V AC	15A 120V (switch) 15A 125V (recept.) NEMA 5-15R	15A 120V (switch) 15A 125V (recept.) NEMA 5-15R
Black	—	RCD101BK	RCD103BK	RCD108BKTR	RCD108BK
Gray	—	RCD101GY	RCD103GY	RCD108GYTR	RCD108GY
Ivory	RCD111I	RCD101I	RCD103I	RCD108ITR	RCD108I
Light Almond	RCD111LA	RCD101LA	RCD103LA	RCD108LATR	RCD108LA
White	RCD111W	RCD101W	RCD103W	RCD108WTR	RCD108W

Description	Two (2) Three Way Switches	 * Three Way Switch, Tamper-Resistant, 2 Pole, 3 Wire, Receptacle	Three Way Switch, 2 Pole, 3 Wire Receptacle	Single Pole Switch, Pilot Light, Clear Lens, Amber Neon Bulb	Three Way Switch, Pilot Light, Clear Lens, Amber Neon Bulb
	Termination	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire
Rating	15A 120-277V AC	15A 120V (switch) 15A 125V (recept.) NEMA 5-15R	15A 120V (switch) 15A 125V (recept.) NEMA 5-15R	15A 120V	15A 120V
Black	RCD303BK	RCD308BKTR	RCD308BK	—	—
Gray	RCD303GY	RCD308GYTR	RCD308GY	—	—
Ivory	RCD303I	RCD308ITR	RCD308I	RCD109I	RCD309I
Light Almond	RCD303LA	RCD308LATR	RCD308LA	RCD109LA	RCD309LA
White	RCD303W	RCD308WTR	RCD308W	RCD109W	RCD309W

Note: *See Technical section, page 10 for Tamper-Resistant description.

Pilot Light Wiring Diagram

