

Duplex Receptacles, 2 Pole, 3 Wire

Description	Standard	Weather and Tamper-Resistant	Tamper-Resistant	Standard
		Termination	Grounding, Push and Side Wire	
Rating	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R
Black	RR15BK	RR15SBKWRTR	RR15SBKTR	RR15SBK
Brown	RR15	RR15SWRTR	RR15STR	RR15S
Ivory	RR15I	RR15SIWRTR	RR15SITR	RR15SI
Light Almond	RR15LA	RR15SLAWRTR	RR15SLATR	RR15SLA
White	RR15W	RR15SWWRTR	RR15SWTR	RR15SW



RR15W

Description	Tamper-Resistant,	Tamper-Resistant, Without Ears*	Standard, Without Ears*
	Termination	Eight Push Wire Holes Only #14 AWG	
Rating	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R
Black	RR15EBKTR	—	—
Brown	RR15ETR	RR15KTR	RR15K
Gray	RR15EGYTR	—	—
Ivory	RR15EITR	RR15KITR	RR15KI
Light Almond	RR15ELATR	RR15KLATR	—
White	RR15EWTR	RR15KWTR	RR15KW



RR15EWTR

Note: See page Tech-10 for Weather and Tamper-Resistant descriptions.
*100 per case, bulk packed. Mounting screws inserted into strap.



RR15KW

Single Receptacles, 2 Pole, 3 Wire

Description	Weather and Tamper-Resistant	Tamper-Resistant	Standard	Weather Resistant	Standard
	Termination	Self-Grounding, Side Wire		Self-Grounding, Side Wire	
Rating	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R	15A 250V NEMA 6-15R	15A 250V NEMA 6-15R
Black	RR151BKWRTR	RR151BKTR	RR151BK	RR155BKWR	RR155BK
Brown	RR151WRTR	RR151TR	RR151	RR155WR	RR155
Gray	RR151GYWRTR	RR151GYTR	RR151GY	RR155GYWR	RR155GY
Ivory	RR151IWRTR	RR151ITR	RR151I	RR155IWR	RR155I
Light Almond	RR151LAWRTR	RR151LATR	RR151LA	RR155LAWR	RR155LA
White	RR151WWRTR	RR151WTR	RR151W	RR155WWR	RR155W



RR151W

Description	Weather and Tamper-Resistant	Tamper-Resistant	Standard	Weather Resistant	Standard
	Termination	Self-Grounding, Side Wire		Self-Grounding, Side Wire	
Rating	20A 125V NEMA 5-20R	20A 125V NEMA 5-20R	20A 125V NEMA 5-20R	20A 250V NEMA 6-20R	20A 250V NEMA 6-20R
Black	RR201BKWRTR	RR201BKTR	RR201BK	RR205BKWR	RR205BK
Brown	RR201WRTR	RR201TR	RR201	RR205WR	RR205
Gray	RR201GYWRTR	RR201GYTR	RR201GY	RR205GYWR	RR205GY
Ivory	RR201IWRTR	RR201ITR	RR201I	RR205IWR	RR205I
Light Almond	RR201LAWRTR	RR201LATR	RR201LA	RR205LAWR	RR205LA
White	RR201WWRTR	RR201WTR	RR201W	RR205WWR	RR205W



RR201W

Note: See page Tech-10 for Weather and Tamper-Resistant descriptions.