



### 15A 125V AC Twist-Lock® Devices

| Description   | Catalog Number    |
|---|-------------------|
| Yellow duplex receptacle has heat resistant body. IP20 suitability.   | <b>HBL47CM00</b>  |
| Yellow Valox® spring-loaded lift cover for weatherproofing duplex receptacles. Stainless steel screws and neoprene gasket included for mounting to FS/FD type weatherproof boxes. IP20 suitability.   | <b>HBL52CM21</b>  |
| Same as HBL52CM21 except white in color.  | <b>HBL52CM21W</b> |
| Same as HBL52CM21 except gray in color.   | <b>HBL5221</b>    |
| Same as HBL52CM21 except for mounting to standard boxes.  | <b>HBL52CM22</b>  |
| Same as HBL52CM22 except gray in color.   | <b>HBL5222</b>    |
| Yellow Insulgrip® plug has rugged nylon housing and detachable cord grip with range of .30-.69 in. (7.5-17.4) that utilizes a unique offset jaws arrangement to provide secure strain relief. IP20 suitability.   | <b>HBL47CM20C</b> |
| Short yellow Seal-Tite® cover for weatherproofing HBL47CM20C Insulgrip plug when used with receptacles or connector bodies. Also can be used to weatherproof HBL47CM29C Insulgrip connector body when used with HBL47CM16 flanged inlet. IP44 SUITABILITY.  | <b>HBL60CM23+</b> |
| Yellow Insulgrip connector body has rugged nylon housing and detachable cord grip with range of .30-.69 in. (7.5-17.4) that utilizes a unique offset jaws arrangement to provide secure strain relief. IP20 suitability.                                    | <b>HBL47CM29C</b> |
| Yellow Seal-Tite cover for weatherproofing HBL47CM29C Insulgrip connector body when used on extension cords and adapters. IP20 SUITABILITY.   | <b>HBL60CM24+</b> |
| Panel mount flanged outlet has heat resistant melamine interior and stainless steel casing. IP20 SUITABILITY.   | <b>HBL47CM15</b>  |
| Panel mount flanged inlet has heat resistant melamine interior and stainless steel casing. IP20 SUITABILITY.  | <b>HBL47CM16</b>  |
| Three conductor, #14 AWG type STW, yellow PVC jacketed portable cord has jute fillers for added flexibility and is ideal for making cable sets, extension cords and adapters as it will not mark the boat's deck. Available in 250 ft. (76.2m) length only. | <b>YC314250</b>   |

Note: +Boots are not UL Listed.



HBL47CM00



HBL52CM21



HBL47CM20C



HBL60CM23



HBL47CM29C



HBL47CM15



HBL47CM16



YC314250



HBL60CM24

Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.