

inREACH™ Industrial and Industrial Weatherproof Cord Reels

Hubbell's newly redesigned inREACH™ Industrial and Industrial Weatherproof Cord Reels improve existing user safety and maximize efficiency by managing cord and power in a safe and organized manner, while also meeting the most demanding industrial environments needs for years with little to no maintenance.

inREACH™ Industrial and Industrial Weatherproof Cord Reels are listed to UL 355 and CSA, C22.2 No. 308 with a durable, lightweight low profile cast aluminum construction. inREACH™ Reels also feature a newly designed mounting plate that allows for a quick easy installation on any surface.

inREACH™ *No matter what your need, Hubbell will always be inREACH™!*

inREACH™ Industrial and Industrial Weatherproof Cord Reels

- » Durable, corrosion resistant cast aluminum construction
- » Yellow or white powder coat finish
- » Multi-position guide arm can be mounted in two positions
- » Positive latch mechanism automatically maintains desired cord length
- » Ratchet lock can be disengaged in field for constant tension applications
- » 16–10 AWG, 3 & 4 conductor cord for greater current carrying capacity
- » Available in 25ft, 35ft and 45ft lengths



HBLI45163



HBLI45123



HBLI45103Y

inREACH™ Industrial Cord Reels

Description	Amps	Volts AC	Cable Length Feet (m)	Cable Type	Weight Lbs. (kg)	White Reel	Yellow Reel
Industrial Reel	10	250	45 (13.7)	16/3 SJO	22.9 (10.4)	HBLI45163	HBLI45163Y
				16/4 SJO	23.6 (10.7)	HBLI45164	HBLI45164Y
			35 (10.7)	16/3 SJO	22.0 (10.0)	HBLI35163	HBLI35163Y
				16/4 SJO	22.7 (10.3)	HBLI35164	HBLI35164Y
			25 (7.6)	16/3 SJO	21.2 (9.6)	HBLI25163	HBLI25163Y
				16/4 SJO	21.8 (9.9)	HBLI25164	HBLI25164Y
Industrial Reel	15	250	45 (13.7)	14/3 SJO	24.0 (10.9)	HBLI45143	HBLI45143Y
				14/4 SJO	25.4 (11.5)	HBLI45144	HBLI45144Y
			35 (10.7)	14/3 SJO	22.9 (10.4)	HBLI35143	HBLI35143Y
				14/4 SJO	24.0 (10.9)	HBLI35144	HBLI35144Y
			25 (7.6)	14/3 SJO	21.8 (9.9)	HBLI25143	HBLI25143Y
				14/4 SJO	22.7 (10.3)	HBLI25144	HBLI25144Y
Industrial Reel	20	250	45 (13.7)	12/3 SJO	26.5 (12.0)	HBLI45123	HBLI45123Y
				12/4 SJO	29.8 (13.5)	HBLI45124	HBLI45124Y
			35 (10.7)	12/3 SJO	24.9 (11.3)	HBLI35123	HBLI35123Y
				12/4 SJO	26.5 (12.0)	HBLI35124	HBLI35124Y
			25 (7.6)	12/3 SJO	23.4 (10.6)	HBLI25123	HBLI25123Y
				12/4 SJO	24.5 (11.1)	HBLI25124	HBLI25124Y
Industrial Reel	30	250	45 (13.7)	10/3 SJO	32.4 (14.7)	HBLI45103	HBLI45103Y
				10/4 SJO	33.7 (15.3)	HBLI40104	HBLI40104Y
			35 (10.7)	10/3 SJO	30.0 (13.6)	HBLI35103	HBLI35103Y
				10/4 SJO	32.2 (14.6)	HBLI35104	HBLI35104Y
			25 (7.6)	10/3 SJO	26.0 (11.8)	HBLI25103	HBLI25103Y
				10/4 SJO	29.1 (13.2)	HBLI25104	HBLI25104Y

Dimensions in Inches (mm)