

Cable, Cord and Hose Reels



Features and Benefits

inREACH™ Industrial Cord Reels

- Durable, corrosion resistant cast aluminum construction
- Yellow or white powder coat finish
- Multi-position guide arm can be mounted in two positions
- Positive latch mechanism automatically maintains desired cord length
- Ratchet lock can be disengaged in field for constant tension applications
- 16–10 AWG, 3 & 4 conductor cord for greater current carrying capacity
- Available in 25ft, 35ft and 45ft lengths



HBLI45123C20

inREACH™ Industrial Cord Reels Connector Ends

Description		Amps	Volts AC	Cable Length		Weight Lbs. (kg)	Catalog Number
				Feet (m)	Cable Type		
White Industrial Reel	with HBL5269C	15	125	45 (13.7)	14/3 SJO	24.0 (10.9)	HBLI45143C15
	with HBL5369C	20	125	45 (13.7)	12/3 SJO	26.5 (12.0)	HBLI45123C20
	with HBL2313					26.5 (12.0)	HBLI45123TL20
White Industrial Reel with Yellow Portable Outlet Box	(1) 15A Duplex Receptacle	15	125	45 (13.7)	14/3 SJO	26.5 (12.0)	HBLI45143R15
	(2) 15A Duplex Receptacles					26.5 (12.0)	HBLI45143R215
	GFCI Module and (1) 15A Duplex Receptacle	15	125	45 (13.7)	14/3 SJO	26.5 (12.0)	HBLI45143GF15
	GFCI Module and (2) 15A Duplex Receptacles					26.5 (12.0)	HBLI45143GF215
White Industrial Reel with Black Portable Outlet Box	(1) 15A Duplex Receptacle	15	125	45 (13.7)	14/3 SJO	26.5 (12.0)	HBLI45143R15M1
	(2) 15A Duplex Receptacles					26.5 (12.0)	HBLI45143R215M1
	GFCI Module and (2) 15A Duplex Receptacles	15	125	45 (13.7)	14/3 SJO	26.5 (12.0)	HBLI45143GF215M1
White Industrial Reel with Yellow Portable Outlet Box	(1) 20A Duplex Receptacle	20	125	45 (13.7)	12/3 SJO	26.5 (12.0)	HBLI45123R20
	(2) 20A Duplex Receptacles					26.5 (12.0)	HBLI45123R220
	GFCI Module and (1) 20A Duplex Receptacle	20	125	45 (13.7)	12/3 SJO	26.5 (12.0)	HBLI45123GF20
	GFCI Module and (2) 20A Duplex Receptacles					26.5 (12.0)	HBLI45123GF220
White Industrial Reel with Black Portable Outlet Box	(1) 20A Duplex Receptacle	20	125	45 (13.7)	12/3 SJO	26.5 (12.0)	HBLI45123R20M1
	(2) 20A Duplex Receptacles					26.5 (12.0)	HBLI45123R220M1
	GFCI Module and (2) 20A Duplex Receptacles	20	125	45 (13.7)	12/3 SJO	26.5 (12.0)	HBLI45123GF220M1



HBLI45143C15



HBLI45123TL20



HBLI45123R20



HBLI45123R20M1

Note: 15A reels are supplied with HBL5266C on the power supply cord. 20A reels are supplied with HBL5366C on the power supply cord. For shorter cable lengths, modify length indication in catalog number (i.e. HBL1XX); 35ft & 25ft lengths are available. For yellow reel, add 'Y' suffix to catalog number.

inREACH™ Accessories

Description	Weight Lbs. (kg)	Catalog Number
Mounting bracket	2.5 (1.1)	HBLIMB
340° pivot base	3.5 (1.1)	HBLI340PB
Replacement stop.	.2 (.09)	HBLI16BS
		HBLI14BS
		HBLI12BS
		HBLI10BS



HBLIMB



HBLI340PB



HBLI16BS



HBLI45123GF20



HBLI45123GF220M1

Dimensions in Inches (mm)

Labor Savings are inREACH™!

