

Cable, Cord and Hose Reels



Features and Benefits

inREACH™ Industrial Weatherproof Cord Reels

- UL Type 4
- 600V AC, SOW Type Cable
- Durable, corrosion resistant cast aluminum construction design with yellow or white powder coat finish
- Multi-position guide arm
- Positive-latch mechanism automatically maintains desired cord length
- 16–10 AWG, 3 & 4 conductor cord for greater current carrying capacity



HBLW45103

inREACH™ Industrial Weatherproof Cord Reels



HBLW45163W



HBLW35143



HBLW45103

Description	Amps	Volts AC	Cable Length Feet (m)	Cable Type	Weight Lbs. (kg)	Yellow Reel	White Reel
Weatherproof Industrial Reel	10	600	45 (13.7)	16/3 SOW	23.6 (10.7)	HBLW45163	HBLW45163W
				16/4 SOW	25.6 (11.6)	HBLW45164	HBLW45164W
	35 (10.7)	16/3 SOW	22.5 (10.2)	HBLW35163	HBLW35163W		
		16/4 SOW	23.1 (10.5)	HBLW35164	HBLW35164W		
	25 (7.6)	16/3 SOW	21.4 (9.7)	HBLW25163	HBLW25163W		
		16/4 SOW	21.8 (9.9)	HBLW25164	HBLW25164W		
Weatherproof Industrial Reel	15	600	45 (13.7)	14/3 SOW	28.2 (12.8)	HBLW45143	HBLW45143W
				14/4 SOW	30.0 (13.6)	HBLW45144	HBLW45144W
	35 (10.7)	14/3 SOW	25.1 (11.4)	HBLW35143	HBLW35143W		
		14/4 SOW	26.5 (12.0)	HBLW35144	HBLW35144W		
	25 (7.6)	14/3 SOW	22.5 (10.2)	HBLW25143	HBLW25143W		
		14/4 SOW	24.3 (11.0)	HBLW25144	HBLW25144W		
Weatherproof Industrial Reel	20	600	45 (13.7)	12/3 SOW	31.3 (14.2)	HBLW45123	HBLW45123W
				12/4 SOW	32.2 (14.6)	HBLW40124	HBLW40124W
	35 (10.7)	12/3 SOW	28.9 (13.1)	HBLW35123	HBLW35123W		
		12/4 SOW	30.6 (13.9)	HBLW35124	HBLW35124W		
	25 (7.6)	12/3 SOW	24.9 (11.3)	HBLW25123	HBLW25123W		
		12/4 SOW	27.6 (12.5)	HBLW25124	HBLW25124W		
Weatherproof Industrial Reel	30	600	40 (12.2)	10/3 SOW	33.3 (15.1)	HBLW40103	HBLW40103W
				10/4 SOW	34.2 (15.5)	HBLW35103	HBLW35103W
	35 (10.7)	10/3 SOW	31.7 (14.4)	HBLW35103	HBLW35103W		
		10/4 SOW	34.2 (15.5)	HBLW35104	HBLW35104W		
	25 (7.6)	10/3 SOW	28.4 (12.9)	HBLW25103	HBLW25103W		
		10/4 SOW	30.2 (13.7)	HBLW25104	HBLW25104W		

inREACH™ Accessories

Description	Weight Lbs. (kg)	Catalog Number
Mounting bracket	2.5 (1.1)	HBLIMB
340° pivot base	3.5 (1.1)	HBLI340PB
Replacement stop.	.2 (.09)	HBLI16BS
		HBLI14BS
		HBLI12BS
		HBLI10BS

HBLIMB

HBLI340PB

HBLI16BS

Labor Savings are inREACH™!



Dimensions in Inches (mm)