

## Gangable AV and Large Capacity Wall Boxes



**HBL985 and HBL986 with HBL989 Low Voltage Partition**



**HBL985**



**HBL986**



**HBL989**

### Gangable AV Wall Boxes

Box	Dimensions	Top Knockouts	Bottom Knockouts	Back Knockouts	Catalog Number
2-Gang, 2 in. KO, 54 in. <sup>3</sup> capacity	H: 4.21 in. W: 4.06 in. D: 4.0 in.	(2) ½" (2) ½" - ¾" TKO*	(1) 1", 1¼", 1½" and 2"	(2) ½" - ¾" TKO	<b>HBL985</b>
3-Gang, 2 in. KO, 79 in. <sup>3</sup> capacity	H: 4.21 in. W: 5.87 in. D: 4.0 in.	(3) ½" (3) ½" - ¾" TKO*	(1) ½" (1) ½" - ¾" TKO* (1) 1", 1¼", 1½" and 2"	(3) ½" - ¾" TKO	<b>HBL986</b>
4-Gang, 2 in. KO, 104 in. <sup>3</sup> capacity	H: 4.21 in. W: 7.69 in. D: 4.0 in.	(4) ½" (4) ½" - ¾" TKO*	(1) ½" (1) ½" - ¾" TKO* (2) 1", 1¼", 1½" and 2"	(4) ½" - ¾" TKO	<b>HBL987</b>
6-Gang, 2 in. KO, 154 in. <sup>3</sup> capacity	H: 4.21 in. W: 11.31 in. D: 4.0 in.	(6) ½" (6) ½" - ¾" TKO*	(1) ½" (1) ½" - ¾" TKO* (2) 1", 1¼", 1½" and 2"	(6) ½" - ¾" TKO	<b>HBL988</b>

Note: UL File Number E31999.  
\*TKO (Tangential Knockout).

### Low Voltage AV Wallbox Partitions

Compatible With	Compatible Mud Ring Depth	Description	Quantity	Catalog Number
HBL985 and HBL986	½", ¾" and 1¼"	Solid divider	1	<b>HBL989</b>
		With pass-thru capability	1	<b>HBL989AVD</b>



Front



Back (Cutaway)



Front



Back (Cutaway)



**HBL260**

Note: Cutaway images are for demonstration purposes only.

### 2-Gang Large Capacity Wall Box - 66.7 Cubic Inch Capacity

Description	Dimensions	Knockouts Sides*	Knockouts Back*	Catalog Number
Square 2-gang wall box	4 <sup>1</sup> / <sub>16</sub> " H x 4 <sup>1</sup> / <sub>16</sub> " W x 3 <sup>3</sup> / <sub>4</sub> " D	(2) ¾" - 1" TKO; (2) 1" - 1¼" TKO; (2) 1" - 2" conc. KO	(2) ¾" - 1" TKO (2) ½" TKO	<b>HBL260</b>

Note: Use with industry standard 4<sup>1</sup>/<sub>16</sub>" square mud rings for 1- or 2-gang applications.  
\*TKO (Tangential Knockout)

### 3-Gang Large Capacity Wall Box - 113.3 Cubic Inch Capacity

Description	Dimensions	Knockouts Sides	Knockouts Back	Catalog Number
Square 2 or 3-gang wall box	4 <sup>1</sup> / <sub>16</sub> " H x 7 <sup>3</sup> / <sub>4</sub> " W x 3 <sup>3</sup> / <sub>4</sub> " D	(4) ½" - ¾" TKO, (4) ¾" - 1" TKO, (2) 1" - 1¼" TKO, (2) 1" - 2" conc. KO	(2) ½" - ¾" TKO, (2) ¾" - 1" TKO, (2) 1" - 1¼" TKO	<b>HBL263</b>

Note: Use with industry standard 4" square mudrings for 1- or 2-gang applications.

### 2-Gang Mud Rings - Compatible with HBL260

Description	Capacity (cu. in.)	Catalog Number
¾" height	7.3	<b>HBL818</b>
¾" height	8.8	<b>HBL840</b>
1" height	12.0	<b>HBL819</b>
1¼" height	15.0	<b>HBL820</b>

### 3-Gang Mud Rings - Compatible with HBL263

Description	Capacity (cu. in.)	Catalog Number
½" height	10.1	<b>HBL792</b>
¾" height	12.3	<b>HBL793</b>
1¼" height	24.3	<b>HBL794</b>



**HBL263**



**HBL792**



**HBL793**



**HBL794**

### Low Voltage Partitions

Compatible With	Compatible Mud Ring Depth	Description	Quantity	Catalog No.
HBL260 and HBL263	½", ¾" and 1¼"	Solid divider	1	<b>HBL981</b>
		With pass-thru capability	1	<b>HBL981AVD</b>