

HBL500, HBL700 and HBL750 Series

| Elbows | Description | Color | HBL500 Series | HBL700 and HBL750 Series | Description | Color | HBL500, HBL700 & HBL750 Series |
|--------|--|----------------|--|--|---|--------------------------------------|--|
| | Internal Elbow For inside surfaces at right angles. | Ivory White | HBL517IV HBL517W A: 3.33" (84.51) B: .58" (14.73) C: 3.33" (84.51) | HBL717IVA HBL717WA A: 3.33" (84.51) B: .90" (22.86) C: 3.33" (84.51) | Internal Elbow Bend Radius For inside surface at right angles requiring a 1.5 in. (38.10) bend radius. Suitable for Category 5, 5e, 6 and 6A applications. | Ivory White | HBL5717BRIVA — A: 3.33" (84.51) B: .91" (23.11) C: 3.33" (84.51) |
| | External Elbow For outside surfaces at right angles. | Ivory White | HBL518IV HBL518W A: 2.59" (65.71) B: .58" (14.73) C: 2.59" (65.71) | HBL718IVA HBL718WA A: 2.59" (65.71) B: .90" (22.86) C: 2.59" (65.71) | External Elbow Bend Radius For outside surfaces at right angles requiring a 1.5 in. (38.10) bend radius. Suitable for Category 5, 5e, 6 and 6A applications. | Ivory White | HBL5718BRIVA — A: 4.86" (123.43) B: .78" (19.80) C: 1.35" (34.28) |
| | 90° Flat Elbow For right angle turns on same surface. | Ivory White | HBL511IV HBL511W A: 2.68" (68.13) B: .61" (15.50) C: 2.68" (68.13) | HBL711IVA HBL711WA A: 2.68" (68.13) B: .90" (22.86) C: 2.68" (68.13) | Flat Elbow Bend Radius For right angle turns requiring a 1.5 in. (38.10) bend radius. Suitable for Category 5, 5e, 6 and 6A applications. | Ivory White | HBL5711BRIVA — A: 3.16" (80.34) B: .91" (23.11) C: 3.16" (80.34) |
| | 45° Flat Elbow For diagonal 45° turns on same surface. | Ivory White | HBL512IV — A: 2.46" (62.61) B: .58" (14.73) C: 2.46" (62.61) | HBL712IVA — A: 2.70" (68.49) B: .91" (23.06) C: 2.70" (68.49) | Internal Twisted Elbows For 90° twist with 90° turn. For double turn at right angles from one to another. From a flat run on a side wall to a flat run on a ceiling, edge of door or window trim. | Ivory White Ivory White | Right Elbow HBL5711RHIVA HBL5711RHWA Left Elbow HBL5711LHIVA HBL5711LHWA A: 2.98" (75.72) B: .94" (23.75) C: 3.00" (76.20) |

| Tees | Description | Color | HBL500, HBL700 & HBL750 Series | Description | Color | HBL500, HBL700 & HBL750 Series |
|------|---|----------------|---|---|----------------|--|
| | Tee Fitting For branches at right angles. | Ivory White | HBL5715IVA HBL5715WA A: 3.06" (77.67) B: 1.14" (28.86) C: 3.03" (76.96) | Tee Fitting Bend Radius For branches at right angles requiring a 1.5 in. (38.10) bend radius. Suitable for Category 5, 5e, 6 and 6A applications. | Ivory White | HBL5715BRIVA — A: 5.55" (140.88) B: .90" (22.86) C: 3.16" (80.34) |

| Fittings | Description | Color | HBL500, HBL700 & HBL750 Series | Description | Color | HBL500, HBL700 & HBL750 Series |
|----------|--|----------------|---|--|----------------|---|
| | Support Clip For supporting lengths of HBL500, HBL700 or HBL750 Raceway. | Ivory White | HBL5703IV HBL5703W A: 2.51" (63.75) | Flexible Section For getting around offsets, side bends, twisted turns or curved surfaces. | Ivory White | HBL5700FIVA HBL5700FWA A: 18.00" (457.20) |

Dimensions in Inches (mm)