



LIST OF PARTS


DESCRIPTION	MATERIAL	FINISH
FLOOR BOX	STEEL	PRE-GALVANIZED
WIRE BARRIER	STEEL	PRE-GALVANIZED
#6-32 BINDING SCREW	CRS	ZINC PLATED
TOP MOUNTING ASSY.	STEEL	ZINC PLATED
#8-32 FLAT HEAD SCREW	CRS	ZINC PLATED
#12 AWG GROUND WIRE & SCR ASSY	COPPER	
PRE-POUR LEVELING SCREW	STEEL WIRE	ZINC PLATED
METAL CONCRETE COVER	STEEL	PRE-GALVANIZED
PLASTIC CONCRETE COVER	POLYPROPYLENE	
REMOVABLE COVER	STEEL	PRE-GALVANIZED OR GREEN FINISH
#10-32 HEX SCREW	STEEL	ZINC PLATED




ISO VIEWS



2 COMPARTMENT
FLOOR BOX
(SHALLOW)



2 COMPARTMENT
FLOOR BOX
(DEEP)



- NOTES: UNLESS OTHERWISE SPECIFIED:
- DIMENSIONS SHOWN ON THIS DRAWING ARE NOMINAL VALUES FOR GENERAL USE ONLY. ACTUAL PART TOLERANCES MUST BE OBTAINED FROM HUBBELL ENGINEERING.
 - PRODUCT IS cULus LISTED.
 - DIMENSIONS ARE IN INCHES [mm].

K.O. TRADE SIZE	LOCATION	QTY
1/2, 3/4, 1	FRONT	2
1/2, 3/4, 1	BACK	2
1/2, 3/4, 1	BOTTOM	8
1/2, 3/4, 1	SIDES	8

K.O. TRADE SIZE	LOCATION	QTY
1, 1-1/4, 1-1/2, 2	FRONT	2
1, 1-1/4, 1-1/2, 2	BACK	2
1/2, 3/4	BOTTOM	2
3/4, 1	SIDES	2

TITLE 2 GANG CONCRETE FLOOR BOX DEEP & SHALLOW

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
.XX ± .01		DR. BY MJM	APP. BY
.XXX ± .005		TR. BY	SCALE 1/4
ANGLES ± 2°		CHK. BY	DATE 1/11/12