



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
FLOOR BOX	STEEL	PRE-GALVANIZED
TOP MOUNTING ASSY.	STEEL	PRE-GALVANIZED
#8-32 FLAT HEAD SCREW	CRS	ZINC PLATE
#12 AWG GROUND WIRE & SCR ASSY.	COPPER	
PRE-POUR LEVELING SCREW	STEEL WIRE	ZINC PLATE
WIRE BARRIER	STEEL	PRE-GALVANIZED
#6-32 BINDING SCREW	STEEL	ZINC PLATE
METAL CONCRETE COVER	STEEL	PRE-GALVANIZED
PLASTIC CONCRETE COVER	POLYPROPYLENE	
DIVIDER 4 GANG	PET	




ISO VIEWS



4 COMPARTMENT FLOOR BOX

4 COMPARTMENT FLOOR BOX



BACK

SIDE

FRONT

SIDE

4X REMOVABLE PLATE

SCREW ADJUSTMENT

SHALLOW BOX

DEEP BOX

CATALOG NO.

CFB4G25

CFB4G25CR

CATALOG NO.

CFB4G30

CFB4G30CR

K.O. TRADE SIZE	LOCATION	QTY
1/2, 3/4, 1	FRONT	2
1/2, 3/4, 1	BACK	2
1/2, 3/4, 1	BOTTOM	8
1/2, 3/4, 1	SIDES	8

NOTES: UNLESS OTHERWISE SPECIFIED:
 1. DIMENSIONS SHOWN ON THIS DRAWING ARE NOMINAL VALUES FOR GENERAL USE ONLY. ACTUAL PART TOLERANCES MUST BE OBTAINED FROM HUBBELL ENGINEERING.
 2. PRODUCT IS CULUS LISTED.
 3. DIMENSIONS ARE IN INCHES [mm].

K.O. TRADE SIZE	LOCATION	QTY
1, 1-1/4, 1-1/2	FRONT	2
1, 1-1/4, 1-1/2	BACK	2
1/2, 3/4, 1	BOTTOM	2
1/2, 3/4, 1	SIDES	2

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
 4 GANG CONCRETE BOX ASSY.
 SHALLOW & DEEP

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
.XX = ± .01	DR. BY MJM	APP. BY
.XXX = ± .005	TR. BY	SCALE 1/4
ANGLES = ± 2°	CHK. BY	DATE 1/11/12