

M-12362

2


CONCENTRIC KNOCKOUTS

LOCATION	QUANTITY	TRADE SIZE
ENDS	2/END	3/4", 1", 1-1/4", 1-1/2"
SIDES	4/SIDE	3/4", 1", 1-1/4", SEE NOTE 7
BOTTOM	4	3/4", 1", 1-1/4", 1-1/2"
BOTTOM	4	1/2", 3/4"

LIST OF PARTS


DESCRIPTION	MATERIAL	FINISH
BOX ASSEMBLY	16 GA. STEEL	ZINC **
DIVIDERS	THERMOPLASTIC	
TOP MOUNTING ASSY	14 GA. STEEL	ZINC
TRANSITION ASSY	14 GA. STEEL	ZINC
GROUND WIRES	COPPER	
KNOCKOUT PLATES	16 GA. STEEL	ZINC
WIRING CHANNEL	16 GA. STEEL	ZINC
FASTENERS	STEEL	ZINC
TEMPORARY COVER	14 GA. STEEL	ZINC

** CATALOG NO. CFB6G30RCR BOX ASSEMBLY IS GALVANIZED AND EPOXY COATED ON EXTERIOR SURFACE.



TOP VIEW


WIRING CHANNEL



REMOVABLE DIVIDERS


SECTION A-A

VIEW THROUGH BOX BELOW TRANSITION



END VIEW

.00 - .25 [0.0 - 6.4]
SUPPORT COLLAR ADJUSTABILITY




4X 1.38 [35.1]
LEVELING SCREW

SIDE VIEW
TEMPORARY COVER NOT SHOWN

KO PLATES

TEMPORARY COVER



ISOMETRIC

NOTES:

1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS].
2. PRODUCT IS cULus LISTED. COMPLIES WITH UL 514A.
3. EACH GANG SUPPLIED WITH 6" [152.4] 12 GA. AWG GROUND PIGTAIL.
4. MINIMUM CONCRETE POUR: 3.75" [95.3].
5. WIRING CHAMBER VOLUMES : (2) END: 89 IN³ [1458 CM³], (4) SIDE: 33 IN³ [540 CM³].
6. WIRING CHANNEL AREA: (2) .40 IN² [261 MM²].
7. 2" TRADE SIZE CONDUIT HUBS (CFBHUB2) MAY BE USED IN PLACE OF SIDE KO PLATES, SOLD SEPARATELY.

CODE 74545

DIMENSION SHEET FOR CAT. NO.

CFB6G30R, CFB6G30RCR

REPAIRABLE ☐NON-REPAIRABLE ☒

B

M-12362

2

2	REVISED PER DCN20776	SBW	9/11/2014
1	INITIAL RELEASE PER DCN19233	SBW	11/15/2013
SYM	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
CONCRETE FLOOR BOX, 6 GANG FOR
8" ROUND COVER

TOLERANCES UNLESS
OTHERWISE SPECIFIED

.XX = ± .01
.XXX = ± .005
ANGLES = ± 2°

WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT.

DR. BY	SBW	APP. BY
TR. BY		SCALE 1/4
CHK'D BY	SM	DATE 9/19/2013