







TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± 01 .XXX = ± 005 ANGLES = $\pm 2^\circ$	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
	DR. BY MJK	APP. BY DJP
	TR. BY JMN	SCALE NONE
	CHK'D BY DJP	DATE 7/31/00



CAT NO.	CONFIGURATION	RATING	HOUSING		CAT. NO.	CONFIGURATION	RATING	HOUSING	
			MATERIAL	COLOR				MATERIAL	COLOR
					HBL3100P7W		60 A 480 VAC	NYLON	RED
					HBL3100P8V0DC		100 A 550 VDC	PBT	BLACK
HBL3100P3W		100 A 250 VDC	NYLON	BLUE					
HBL3100P4W		100 A 125 VAC	NYLON	YELLOW					
HBL3100P6W		100 A 250 VAC	NYLON	BLUE					
HBL3125P6W		125 A 220-240 VAC							

NOTES: (UNLESS OTHERWISE SPECIFIED)

1) TOLERANCES ARE:

DECIMALS $\pm .03$

ANGLES $\pm 2^\circ$

2) DIMENSIONS ARE INCHES

[MILLIMETERS]