




M-6079 10



CABLE DIA.
1.065 MIN.
[30.48]
1.780 MAX.
[45.21]

NOTES: (UNLESS OTHERWISE SPECIFIED)
1) DIMENSION FORMAT IS: INCHES
[mm]

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
HOUSING	SEE TABLE	
GASKET	RUBBER	
LOCK RING	POLYESTER	
INTERIOR	THERMOSET	
PINS	BRASS	
TERM.SCREWS	STAIN. STEEL	
GLAND CAP	POLYESTER	
GLANDS	RUBBER	
CLAMPS	POLYESTER	
CLAMP NUTS	BRASS	NICKEL
ASS'Y SCRS.	STAIN. STEEL	



CATALOG NO. HBL4100P7W
(NOT SHOW TO SCALE)

CAT NO.	CONFIGURATION	RATING	HOUSING		CAT. NO.		RATING	HOUSING	
			COLOR	MATERIAL				COLOR	MATERIAL
					HBL4100P7V05		100A 3ø 480VAC	RED	POLYBUTYLENE TEREPHTHALATE (PBT)
					HBL4100P7WR HBL4100P7W			RED	NYLON
					HBL4100P9WR HBL4100P9W		100A 3ø 250VAC	BLUE	NYLON
					4100P9V01 HBL4100P9V01			BLUE	POLYBUTYLENE TEREPHTHALATE (PBT)
HBL4100P5WS		100A3ø 600VAC PILOT CONTACT A600	BLACK	NYLON					
HBL4100P5WR HBL4100P5W		100A3ø 600VAC	BLACK	NYLON					
HBL4125P6W		125AMP 380-415VAC	RED	NYLON	HBL4100P12WR HBL4100P12W		100AMP 125/250VAC	ORANGE	NYLON

10	ADDED ISO VIEW TO INDICATE SOLID MODEL EMBEDDED IN DRAWING. PER DCN 21895 DDL	DJP	02/22/16
9	3/8/12 ADDED HBL4100P9V01 PER DCN 18679 SPN	DJP	3/8/12
8	CHANGED MATERIAL FOR HBL4100P7V05 FROM POLYESTER TO POLYBUTYLENE TERE. (PBT) ADDED CAT. 4100P9V01 WITH COLOR AND MATERIAL. PER DCN 17546 SPN	PJB	3/16/11
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE 100A & 125A 3 POLE 4 WIRE PIN & SLEEVE PLUGS

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
.XX = ± .01	DR. BY MJK	APP. BY WES	
.XXX = ± .005	TR. BY CAC	SCALE NONE	
ANGLES = ± 2°	CHK'D BY	DATE 5/13/80	