



# M-6098 5



## LIST OF PARTS

| DESCRIPTION     | MATERIAL  | FINISH |
|-----------------|-----------|--------|
| HOUSING         | SEE TABLE |        |
| GASKET          | NEOPRENE  |        |
| LOCK RING       | POLYESTER |        |
| INTERIOR        | THERMOSET |        |
| PINS            | BRASS     |        |
| TERMINAL SCREWS | ST. STEEL |        |
| FLANGE          | NYLON     |        |
| ASSEMBLY SCREWS | ST. STEEL |        |
|                 |           |        |
|                 |           |        |
|                 |           |        |
|                 |           |        |
|                 |           |        |
|                 |           |        |

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE ☐

NON-REPAIRABLE ☒

B

M-6098

5

| CAT. NO.   | CONFIGURATION | RATING                            | COMMENTS | HOUSING  |       | CAT. NO.   | CONFIGURATION | RATING                  | COMMENTS | HOUSING  |       |
|------------|---------------|-----------------------------------|----------|----------|-------|------------|---------------|-------------------------|----------|----------|-------|
|            |               |                                   |          | MATERIAL | COLOR |            |               |                         |          | MATERIAL | COLOR |
|            |               |                                   |          |          |       | HBL5100B7W |               | 100A 3ØY<br>277/480 VAC |          | NYLON    | RED   |
|            |               |                                   |          |          |       |            |               |                         |          |          |       |
|            |               |                                   |          |          |       | HBL5100B9W |               | 100A 3ØY<br>120/208 VAC |          | NYLON    | BLUE  |
|            |               |                                   |          |          |       |            |               |                         |          |          |       |
| HBL5100B5W |               | 100A 3ØY<br>347/600 VAC           |          | NYLON    | BLACK |            |               |                         |          |          |       |
| HBL5125B6W |               | 125A<br>220/380VAC<br>240/415 VAC |          | NYLON    | RED   |            |               |                         |          |          |       |

### NOTES (UNLESS OTHERWISE SPECIFIED)

1) TOLERANCES ARE:

DECIMALS ± .03  
ANGLES ± 2°

2) DIMENSIONS ARE: INCHES

[MILLIMETERS]

5 REDRAWN ON CAD WITH CHANGES. ADDED NOTES 1 & 2, "HOUSING" AND "COMMENTS" COLUMNS TO TABLE. IN TABLE: ADDED "240/415VAC TO HBL5125B6W AND "A" WAS "AMP" IN LIST OF PARTS, "SEE TABLE" WAS "NYLON" AND "NEOPRENE" WAS "RUBBER". .22 DIM. WAS 7/32 AND 4.87[123.7] SQ. WAS 4.875/123.82 SQ. "Ø" WAS "DIA." AND "[XX.X]" WAS "MM". SUPERSEDES DWG. DATED 5/6/80 PER DCN #12944. JMN

DJP 6/28/06

SYM REVISIONS APP DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE  
100A & 125A 4 POLE 5 WIRE  
PIN AND SLEEVE INLETS

TOLERANCES UNLESS OTHERWISE SPECIFIED  
FRACTIONS 1/64  
DECIMALS ± .005  
ANGLES ± 2°

WIRING DEVICE-KELLEMS  
HUBBELL INCORPORATED  
BRIDGEPORT, CT

DR. BY W.T.C. APP. BY DJP  
TR. BY JMN SCALE NONE  
CHK'D BY DJP DATE 6/28/06