



M-6097 8



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	SEE TABLE	
INTERIOR	THERMOSET	
SLEEVES	BRASS	
SLEEVE INSERT	BERR COPPER	SILVER
TERM. SCRS.	STAIN. STEEL	
COVER	POLYESTER	
COVER SCREWS	BRASS	NICKEL
COVER SPRING	STAIN. STEEL	
GASKET	NEOPRENE	
DISC	POLYCARBONATE	
ARM	POLYESTER	
HINGE PIN	STAIN. STEEL	
HINGE SPR.	STAIN. STEEL	
ASS'Y SCREWS	STAIN. STEEL	

CAT. NO.	CONFIGURATION	RATING	HOUSING		CAT. NO.	CONFIGURATION	RATING	HOUSING	
			MATERIAL	COLOR				MATERIAL	COLOR
					HBL5100R7W		100A 3ØY 277/480 VAC	NYLON	RED
					HBL5100R8WDC		100 A 400 VDC	NYLON	RED
					HBL5100R9W		100A 3ØY 120/208 VAC	NYLON	BLUE
HBL5100R5W		100A 3ØY 347/600 VAC	NYLON	BLACK					
HBL5125R6W		125A 220/380VAC 240/415VAC	NYLON	RED					

NOTES: (UNLESS OTHERWISE SPECIFIED)

- TOLERANCES ARE:
DECIMALS $\pm .03$
ANGLES $\pm 2^\circ$
- DIMENSIONS ARE INCHES
[MILLIMETERS]

SYM	REVISIONS	APP	DATE
-----	-----------	-----	------

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
100A & 125A 4 POLE 5 WIRE
PIN & SLEEVE RECEPTACLE

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRAGMENTS	11/04	DR. BY MJK	APP. BY DJP
DECIMALS	$\pm .03$	TR. BY JMN	SCALE NONE
ANGLES	$\pm 2^\circ$	CHK'D BY DJP.	DATE 6/28/06