


M-7672 2



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
HOUSING	NYLON	
INTERIOR	THERMOSET	
GASKET	RUBBER	
LOCK RING	POLYESTER	
SLEEVES	BRASS	NICKEL
TERMINAL SCREWS	STAIN. STL.	
GLAND CAP	POLYESTER	
GLANDS	RUBBER	
CLAMPS	POLYESTER	
CLAMP NUTS	BRASS	NICKEL
ASSY. SCREWS	STAIN. STL.	

DIMENSION SHEET FOR CAT. NO.

REPAIRABLE NON-REPAIRABLE

B

M-7672

2

CAT. No.	CONFIGURATION	RATING	CAT. No.	CONFIGURATION	RATING
			M5100C7R		100A 3ØY 277/480 VAC
			M5100C9R		100A 3ØY 120/208 VAC

2	ADDED CAT. # M5100C7R. "NICKEL" TO SLEEVE FINISH IN TABLE, AND "(REVERSE SERVICE)" TO TITLE PER DCN #12377. JMN	CJC	6/6/05
1	RELEASED PER DCN 4455/106		8-22-96
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE.

NOTES:
1. ALL DECIMAL DIM. TOLS. TO BE ±.03

TITLE
100A. 5 WIRE
PIN & SLEEVE CONNECTOR
(REVERSE SERVICE)

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE DIVISION HARVEY HUBBELL, INC. BRIDGEPORT, CONN.	
FRACTIONS ± 1/64	DR. BY <i>[Signature]</i>	APP. BY
DECIMALS ± .005	TR. BY	SCALE 1:1
ANGLES ± 2°	CHK'D. BY	DATE 8-22-96