



M-6052 3



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
HOUSING	SEE TABLE	
INTERIOR	THERMOSET	
SLEEVES	BRASS	
SLEEVE SPRINGS	ST. STEEL	
TERMINAL SCREWS	ST. STEEL	
COVER	POLYESTER	
COVER SCREW	BRASS	NICKEL
COVER SPRING	ST. STEEL	
GASKET	NEOPRENE	
DISC	POLYCARBONATE	
ARM	POLYESTER	
HINGE PIN	ST. STEEL	
HINGE SPRING	ST. STEEL	
GLAND CAP	POLYESTER	
GLANDS	NEOPRENE	
CLAMPS	POLYESTER	
CLAMP NUTS	BRASS	NICKEL
ASSEMBLY SCREWS	ST. STEEL	

REPAIRABLE ☐ NON-REPAIRABLE ☒ SEE TABLE

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-6052

3

CAT. NO.	CONFIGURATION	RATING	COMMENTS	HOUSING		CAT. NO.	CONFIGURATION	RATING	COMMENTS	HOUSING	
				MATERIAL	COLOR					MATERIAL	COLOR
						HBL320C7W		20 A 480 VAC		NYLON	RED
HBL320C4W		20 A 125 VAC		NYLON	YELLOW						
HBL316C4W		16 A 110-130VAC									
HBL320C6W		20 A 250 VAC		NYLON	BLUE						
HBL316C6W		16A 220-240VAC									

NOTES (UNLESS OTHERWISE SPECIFIED)

1) TOLERANCES ARE:

DECIMALS $\pm .03$
ANGLES $\pm 2^\circ$

2) DIMENSIONS ARE: INCHES

[MILLIMETERS]

3	REDRAWN ON CAD WITH CHANGES. ADDED "16A" TO DWG. TITLE, "HOUSING" AND "COMMENTS" COLUMNS AND NOTES 1 & 2. IN TABLE, REMOVED CAT. NO. 'S 320C3W, HBL320C5W, & 320C9W "A" WAS "AMP" AND "110-130VAC" WAS "110-120VAC". IN LIST OF PARTS, "SEE TABLE" WAS "NYLON" AND "NEOPRENE" WAS "RUBBER" IN (2) PLACES. "CABLE Ø.330[8.38] MIN./Ø.830[21.08] MAX" WAS "CABLE DIA..360 9.14MM MIN. .780 19.8MM MAX.". "Ø" WAS "DIA." AND "[XX.X]" WAS "MM". SUPERSEDES DRAWING DATED 4/30/80 PER DCN #12944. JMN	DJP	5/30/06
---	---	-----	---------

SYM	REVISIONS	APP	DATE
-----	-----------	-----	------

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE 16A & 20A 2 POLE 3 WIRE
PIN AND SLEEVE
CONNECTORS

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS	$\pm 1/64$	DR. BY	MJK
DECIMALS	$\pm .005$	APP. BY	DJP
ANGLES	$\pm 2^\circ$	TR. BY	JMN
		SCALE	NONE
		CHK'D BY	DJP
		DATE	6/7/06