



M-6067 4



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	SEE TABLE	
GASKET	NEOPRENE	
LOCK RING	POLYESTER	
INTERIOR	THERMOSET	
PINS	BRASS	
TERMINAL SCREWS	ST. STEEL	
GLAND CAP	POLYESTER	
GLANDS	NEOPRENE	
CLAMPS	POLYESTER	
CLAMP NUTS	BRASS	NICKEL
ASSEMBLY SCREWS	ST. STEEL	

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-6067

4

CAT. NO.	CONFIGURATION	RATING	COMMENTS	HOUSING		CAT. NO.	CONFIGURATION	RATING	COMMENTS	HOUSING	
				MATERIAL	COLOR					MATERIAL	COLOR
						HBL420P7W		20 A 3Ø 480 VAC		NYLON	RED
						HBL420P9W		20 A 3Ø 250 VAC		NYLON	BLUE
HBL420P5W		20 A 3Ø 600 VAC		NYLON	BLACK						
HBL416P6W		16 A 380-415 VAC		NYLON	RED	HBL420P12W		20 A 125/250 VAC		NYLON	ORANGE

NOTES (UNLESS OTHERWISE SPECIFIED)

1) TOLERANCES ARE:

DECIMALS ± .03
ANGLES ± 2°

2) DIMENSIONS ARE: INCHES

[MILLIMETERS]

CODE 74545

SYM	REVISIONS	APP	DATE
-----	-----------	-----	------

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
16A & 20A 3 POLE 4 WIRE
PIN AND SLEEVE PLUGS

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS	1/64	DR. BY	MJK
DECIMALS	± .005	APP. BY	DJP
ANGLES	± 2°	TR. BY	JMN
		SCALE	NONE
		CHK'D BY	DJP
		DATE	6/14/06