



M-10831 1



CABLE DIA.
1.0 MIN.
(25.4)

2.5 MAX.
(63.5)

NOTES: (UNLESS OTHERWISE SPECIFIED)

1) DIMENSION FORMAT IS: INCHES
[mm]

TABLE									
AMPS	MAX VOLTAGE AC/DC	CONNECTOR CATALOG NUMBER	PLUG			DIM "A"		DIM "B" Ø	
			STYLE	POLE	WIRE	INS.	mm	INS.	mm
200	600/250	M5200PS1	S1	4P	5W	11.13	282.7	6.70	170.2

CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
O-RING	RUBBER	
SLEEVES	COPPER ALLOY	NICKEL PLATED
LOCK COLLAR	ALUMINUM	
SHROUD	ALUMINUM	
SET SCREW	STAIN STEEL	
SCREWS	STAIN STEEL	
SPRING WASHER	COPPER ALLOY	
GROUND POST	BRASS	
GROUND STRAP	COPPER ALLOY	
PLUG HOUSING	ALUMINUM	YELLOW
CLAMP GUIDE	ALUMINUM	GRAY EPOXY
CLAMP	ALUMINUM	GRAY EPOXY
CLAMP INSERTS	ALUMINUM	GRAY EPOXY
ONION SKIN GROMMET	RUBBER	
INTERIOR	THERMOSET POLYESTER	

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE ☒ NON-REPAIRABLE ☐

B

M-10831

1

1	RELEASED PER DCN #14472 JMN	WUH VH	1/31/08
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
200A MARINE INSULGRIP
PIN & SLEEVE PLUG
STYLE 1

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS ±1/64 DECIMALS ±.005 ANGLES ±2° 2 DECIMALS ±.030	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
	DR. BY JMN	APP. BY WUH
	TR. BY	SCALE 1:2
	CHK'D BY WUH	DATE 1/31/08