





**M-6074 5**

NOTES: (UNLESS OTHERWISE SPECIFIED)

1) DIMENSION FORMAT IS: INCHES  
[mm]

2) DIMENSIONS SHOWN ON THIS DRAWING ARE  
NOMINAL VALUES FOR GENERAL USE ONLY.  
ACTUAL PART TOLERANCES MUST BE  
OBTAINED FROM HUBBELL ENGINEERING.

| LIST OF PARTS  |              |        |
|----------------|--------------|--------|
| DESCRIPTION    | MATERIAL     | FINISH |
| 1. HOUSING     | SEE TABLE    |        |
| 2. GASKET      | RUBBER       |        |
| 3. LOCK RING   | POLYESTER    |        |
| 4. INTERIOR    | THERMOSET    |        |
| 5. PINS        | BRASS        |        |
| 6. TERM. SCRS. | STAIN. STEEL |        |
| 7. FLANGE      | NYLON        |        |
| 8. ASS'Y SCRS. | STAIN. STEEL |        |

| CAT. NO.    | CONFIGURATION | RATING                | HOUSING |       | CAT. NO.   | CONFIGURATION | RATING                | HOUSING |       |
|-------------|---------------|-----------------------|---------|-------|------------|---------------|-----------------------|---------|-------|
|             |               |                       | COLOR   | MAT'L |            |               |                       | COLOR   | MAT'L |
|             |               |                       |         |       | HBL430B7W  |               | 30A 3Ø<br>480 VAC     | RED     | NYLON |
|             |               |                       |         |       |            |               |                       |         |       |
|             |               |                       |         |       | HBL430B9W  |               | 30A 3Ø<br>250 VAC     | BLUE    | NYLON |
|             |               |                       |         |       |            |               |                       |         |       |
| HBL430B5W   |               | 30A 3Ø<br>600 VAC     | BLACK   | NYLON |            |               |                       |         |       |
| HBL432B6W   |               | 32 AMP<br>380-415 VAC | RED     | NYLON | HBL430B12W |               | 30 AMP<br>125/250 VAC | ORANGE  | NYLON |
| HBL430B6V02 |               | 30A<br>380 - 415 VAC  | RED     | VALOX |            |               |                       |         |       |

TITLE

30 & 32 A. 3 POLE 4 WIRE  
PIN & SLEEVE INLETS

TOLERANCES UNLESS  
OTHERWISE SPECIFIED

DECIMALS ± .03  
ANGLES ± 2°

HARVEY HUBBELL, INC.

BRIDGEPORT, CONN.

DR. BY W.T.C. APP. BY

TR. BY SCALE: 1"=1" DATE 5/5/80

CHCD. BY DATE 5/5/80

CODE 74545

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE ☐

NON-REPAIRABLE ☒

B

**M-6074**

5