




NOTES: (UNLESS OTHERWISE SPECIFIED)

1) DIMENSION FORMAT IS: INCHES
[mm]

AMPS	POLES AND WIRES	MAX VOLTAGE AC/DC	STYLE	CONNECTOR CATALOG NUMBER
30	2P3W	600/250	S1	HBL330RS1WR
30	3P4W	600/250	S1	HBL430RS1WR
30	4P5W	600/250	S1	HBL530RS1WR
30	2P3W	600/250	S2	HBL330RS2WR
30	3P4W	600/250	S2	HBL430RS2WR

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
BOX TERMINAL	STEEL	NICKEL PLATE
GROUND STANDOFF	BRASS	
HINGE BUSHING	ALUMINUM	
SPRING GUIDE	STAIN STEEL	
LID SPRING	STAIN STEEL	
LID	ALUMINUM	GRAY EPOXY
LID LIFTER	ALUMINUM	GRAY EPOXY
O-RING	RUBBER	
LID GASKET	RUBBER	
CLAMP NUT	BRASS	NICKEL PLATE
GLAND	RUBBER	
SPRING WASHER	STAIN STEEL	
WAVE SPRING	STAIN STEEL	
RIVET	ALUMINUM	
RECEPTACLE	ALUMINUM	GRAY EPOXY
SCREWS	STAIN STEEL	
SLEEVES	BRASS	
INTERIOR	THERMOSET POLYESTER	
PIN SPRING	COPPER ALLOY	SILVER COATED

2	ADDED TABLE, "SEE TABLE", NOTE 1, "2X" TO 2.72(69) & 3.40(86) AND "Ø 1.885 [47.88]"; DRAWING TITLE WAS "30A PIN & SLEEVE REVERSE RECEPT. ASSEMBLY STYLES 1 & 2"; REMOVED "MM" FROM DIMENSIONS; ADDED "COPPER ONLY" TO "WIRE RANGE #8- #10 AWG"; PER DCN #8695. JMN	TCM	1/24/02
1	NEW RELEASE PER DCN 7013 RTK	RDK	8/23/99
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
30A INSULGRIP PIN & SLEEVE REVERSE SERVICE RECEPTACLE STYLES 1 & 2

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ± 1/64	DR. BY RTK	APP. BY RDK
3DECIMALS ± .005	TR. BY	SCALE 1:1
ANGLES ± 2°	CHK'D BY RDK	DATE 8/23/99
2DECIMALS ± .01		

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE ☒ NON-REPAIRABLE ☐

B

M-8262

N