




NOTES: (UNLESS OTHERWISE SPECIFIED)

1) DIMENSION FORMAT IS: INCHES [mm]

CAT NO.	CONFIGURATION	RATING	HOUSING		CAT. NO.	CONFIGURATION	RATING	HOUSING	
			COLOR	MATERIAL				COLOR	MATERIAL
HBL360P3W		60 AMP 250 VDC	BLUE	NYLON	HBL360P7W		60 AMP 480 VAC	RED	NYLON
HBL360P4W		60 AMP 125 VAC	YELLOW	NYLON	HBL360P7W		60 AMP 480 VAC	RED	PBT
HBL360P4W		60 AMP 125 VAC	YELLOW	PBT	HBL360P7W		A600 PILOT CONTACT	RED	PBT
HBL360P4WP		60 AMP 125 VAC A600 PILOT CONTACT	YELLOW	PBT					
HBL360P6W		60 AMP 250 VAC	BLUE	NYLON					
HBL360P6W HBL360P6V04		60 AMP 250 VAC	BLUE	PBT					
HBL363P6W		60 AMP 250 VAC 63 AMP 220-240 VAC	BLUE	NYLON	HBL360P8V0DC		60 AMP 550 VDC	BLACK	PBT
HBL360P6WP		60 AMP 250 VAC A600 PILOT CONTACT	BLUE	PBT					

CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	SEE TABLE	
GASKET	NEOPRENE	
LOCK RING	POLYESTER	GRAY
INTERIOR	THERMOSET	
PINS	BRASS	
TERM. SCREWS	STAIN. STEEL	
GLAND CAP	POLYESTER	
GLANDS	NEOPRENE	
CLAMPS	POLYESTER	
CLAMP NUTS	BRASS	NICKEL
ASSY SCRS.	STAIN. STEEL	

WHD 2/24/16

11	ADDED ALL HBL CATALOG NO.s PER DCN 21767 WHD	WHD	1/20/16
10	ADDED CATALOG HBL360P6V04 MATERIAL NEOPRENE WAS RUBBER 2 PLACES. PER DCN 19791 SPN	DJP	5/3/13
9	ADDED FINISH FOR LOCK RING PER DCN 19175 RGP	TLS	10/25/12
8	RATING FOR CATALOG HBL360P8V0DC 60A WAS 100A PER DCN 17679 MYA	TLS	7/19/11
7	ADDED POLARITY TO CATALOG HBL360P8V0DC PER DCN 16648 MYA	TLS	5/12/10
6	REMOVED "L1", "G" AND "N" MARKINGS PER DCN 16610 MYA	TLS	4/30/10
5	ADDED CAT. HBL360P8V0DC PER DCN 16502 SPN	MM	4/13/10
4	REDRAWN ON CAD; ADDED NOTE, DIMENSIONS, HOUSING INFO AND L1, N & G TO CONFIGURATION CABLE DIA WAS .875 MIN, 1.280 MAX PER DCN #10349	RDK	10-24-02
3	ADDED "HBL" TO CAT # EC 7185	RDK	10-7-99
2	REMOVED CAT NOS. 360P5W 360P9W	MM	7-17-91 AJL
1	ADDED CAT NO. 363P6W CHANGED FRACTIONAL DIMS. TO DECIMAL DIMS. REVISED LIST OF PARTS	MM	6-22-90 AJL

SYM	REVISIONS	APP	DATE
-----	-----------	-----	------

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE 60A & 63A 2 POLE 3 WIRE PIN & SLEEVE PLUGS

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
FRACTIONS ±1/64	DR. BY MJK	APP. BY
DECIMALS ±.005	TR. BY	SCALE NONE
ANGLES ±2°	CHK'D BY	DATE 4/28/80
DECIMALS ±.03		

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE ☒

NON-REPAIRABLE ☐

B

M-6059

11