



# M-6092 8



| CAT. NO.  | CONFIGURATION | RATING                           | COMMENTS | HOUSING  |       | CAT. NO.    | CONFIGURATION | RATING                                | COMMENTS | HOUSING  |       |
|-----------|---------------|----------------------------------|----------|----------|-------|-------------|---------------|---------------------------------------|----------|----------|-------|
|           |               |                                  |          | MATERIAL | COLOR |             |               |                                       |          | MATERIAL | COLOR |
|           |               |                                  |          |          |       | HBL560C6W   |               | 60A 3ØY<br>200/346 VAC<br>240/415 VAC |          | NYLON    | RED   |
|           |               |                                  |          |          |       | HBL560C7W   |               | 60A 3ØY<br>277/480 VAC                |          | NYLON    | RED   |
|           |               |                                  |          |          |       | HBL560C9W   |               | 60A 3ØY<br>120/208 VAC                |          | NYLON    | BLUE  |
|           |               |                                  |          |          |       |             |               | 60A 3ØY<br>200/346 VAC<br>240/415 VAC |          |          |       |
| HEL560C5W |               | 60A 3ØY<br>347/600 VAC           |          | NYLON    | BLACK | HBL560C6V02 |               | 63A 3ØY<br>200/346 VAC<br>240/415 VAC |          | VALOX    | RED   |
| HEL563C6W |               | 63A<br>220/380VAC<br>240/415 VAC |          | NYLON    | RED   |             |               |                                       |          |          |       |

## NOTES (UNLESS OTHERWISE SPECIFIED)

- TOLERANCES ARE:  
DECIMALS ± .03  
ANGLES ± 2°
- DIMENSIONS ARE: INCHES  
[MILLIMETERS]

CODE 74545

## LIST OF PARTS

| DESCRIPTION     | MATERIAL      | FINISH |
|-----------------|---------------|--------|
| HOUSING         | SEE TABLE     |        |
| INTERIOR        | THERMOSET     |        |
| SLEEVES         | BRASS         |        |
| INSERT SPRINGS  | BERR. COPPER  | SILVER |
| TERMINAL SCREWS | ST. STEEL     |        |
| COVER           | POLYESTER     |        |
| COVER SCREW     | BRASS         | NICKEL |
| COVER SPRING    | ST. STEEL     |        |
| GASKET          | NEOPRENE      |        |
| DISC            | POLYCARBONATE |        |
| ARM             | POLYESTER     |        |
| HINGE PIN       | ST. STEEL     |        |
| HINGE SPRING    | ST. STEEL     |        |
| GLAND CAP       | POLYESTER     |        |
| GLANDS          | NEOPRENE      |        |
| CLAMPS          | POLYESTER     |        |
| CLAMP NUTS      | BRASS         | NICKEL |
| ASSEMBLY SCREWS | ST. STEEL     |        |

|     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |     |         |
|-----|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----|---------|
| 8   | ADDED CAT. #HBL56(C6V02 TO TABLE PER DCN 19871 SPN                                                                                                                                                                                                                                                                                                                                                                                                                          | DJP | 6/6/13  |
| 7   | ADDED CAT # HBL560C6W TO TABLE PER DCN 17473. MYA                                                                                                                                                                                                                                                                                                                                                                                                                           | TLS | 3/11/11 |
| 6   | REDRAWN ON CAD WITH CHANGES. ADDED "HOUSING" & "COMMENTS" COLUMNS TO TABLE, AND NOTES 1 & 2. IN TABLE, REMOVED CAT. NO. HBL560C6W, & ADDED "240/415VAC TO CAT. NO. HBL563C6W; "A" WAS "AMP". IN LIST OF PARTS, "SEE TABLE" WAS "NYLON" AND "NEOPRENE" WAS "RUBBER" IN (2) PLACES. "CABLE Ø.500[12.70] MIN./ Ø1.450[36.80] MAX" WAS "CABLE DIA. 1.00/25.4MM MIN. 1.43[36.3] MAX". "Ø" WAS "DIA." AND "DXX.X]" WAS "MM". SUPERSEDES DRAWING DATED 4/29/80 PER DCN #12944. JMN | DJP | 6/28/06 |
| SYM | REVISIONS                                                                                                                                                                                                                                                                                                                                                                                                                                                                   | APP | DATE    |

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE  
**60A & 63A 4 POLE 5 WIRE  
PIN AND SLEEVE CONNECTORS**

|                                       |                                                                 |     |         |         |
|---------------------------------------|-----------------------------------------------------------------|-----|---------|---------|
| TOLERANCES UNLESS OTHERWISE SPECIFIED | WIRING DEVICE—KELLEMS<br>HUBBELL INCORPORATED<br>BRIDGEPORT, CT |     |         |         |
| FRACTIONS 1/64                        | DR. BY                                                          | MJK | APP. BY | DJP     |
| DECIMALS ± .005                       | TR. BY                                                          | JMN | SCALE   | NONE    |
| ANGLES ± 2°                           | CHK'D BY                                                        | DJP | DATE    | 6/28/06 |

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-6092

8