









CONFIGURATION TABLE				
CAT NO.	CONFIGURATION	RATING	HSG MAT'L	HSG COLOR
HBL5360R4W HBL5360R4WP		60A 125 VAC 60A 125 VAC WITH PILOT/AUX CONTACT	PBT	YELLOW
HBL5360R6W HBL5360R6WP		60A 250 VAC 60A 250 VAC 63A 220-240 VAC WITH PILOT/AUX CONTACT	PBT	BLUE
HBL5360R7W HBL5360R7WP		60A 480 VAC 60A 480 VAC WITH PILOT/AUX CONTACT	PBT	RED
HBL5460R5W HBL5460R5WP		60A 3Φ 600 VAC 60A 3Φ 600 VAC WITH PILOT/AUX CONTACT	PBT	BLACK
HBL5460R6W HBL5460R6WP		60A 380-415 VAC 60A 380-415 VAC 63A 380-415 VAC WITH PILOT/AUX CONTACT	PBT	RED
HBL5460R7W HBL5460R7WP		60A 3Φ 480 VAC 60A 3Φ 480 VAC WITH PILOT/AUX CONTACT	PBT	RED
HBL5460R9W HBL5460R9WP		60A 3Φ 250 VAC 60A 3Φ 250 VAC 63A 3Φ 250 VAC WITH PILOT/AUX CONTACT	PBT	BLUE
HBL5460R12W HBL5460R12WP		60A 125/250 VAC 60A 125/250 VAC WITH PILOT/AUX CONTACT	PBT	ORANGE
HBL5560R5W HBL5560R5WP		60A 3Φ 347/600 VAC 60A 3Φ 347/600 VAC WITH PILOT/AUX CONTACT	PBT	BLACK
HBL5560R6W HBL5560R6WP		60A 200/346 - 240/415 VAC 60A 200/346 - 240/415 VAC 63A 220/415 VAC WITH PILOT/AUX CONTACT	PBT	RED
HBL5560R7W HBL5560R7WP		60A 3Φ 277/480 VAC 60A 3Φ 277/480 VAC WITH PILOT/AUX CONTACT	PBT	RED
HBL5560R9W HBL5560R9WP		60A 3Φ 120/208 VAC 60A 3Φ 120/208 VAC 63A 3Φ 120/208 VAC WITH PILOT/AUX CONTACT	PBT	BLUE

CODE 74545

M-12538

1



3, 4 & 5 WIRE
SWITCHED RECEPTACLE

WHD 3/11/16

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
HOUSING	PBT	
INTERIOR	NYLON	
SLEEVES	BRASS	
PHASE, NEUTRAL & GND CONTACTS	BER. COPPER	SILVER
TERMINAL SCREWS	SS	
HINGE & LID	PBT	
HINGE PIN & SPRING	SS	
ASSY SCREWS	SS	
LED WINDOW	POLYCARBONATE	
HOUSING GASKET	RUBBER	

SEE TABLE			
REPAIRABLE ☐			
NON-REPAIRABLE ☒			

1	RELEASED FOR PRODUCTION PER DCN 21767 WHD 1/27/16		
SYM	DESCRIPTION	APPRO	DATE
THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE			
TITLE 60 & 63A 2W/3P, 3W/4P & 4W/5P PIN & SLEEVE SWITCHED RECEPTACLES			
TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ±.01 .XXX = ±.005 ANGLES = ±2°		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT DR. BY wdietz TR. BY WHD CHK'D BY APP. BY SCALE DATE 9/23/2015	