


M-7863 3



NOTES: (UNLESS OTHERWISE SPECIFIED)

1) DIMENSION FORMAT IS: INCHES
[mm]

AMPS	POLES AND WIRES	MAX VOLTAGE AC/DC	STYLE	Ø "A" [A]	CONNECTOR CATALOG NUMBER
60	2P3W	600/250	S1	2.195 [55.75]	HBL360RS1W
60	3P4W	600/250	S1	2.50 [63.5]	HBL460RS1W
60	2P3W	600/250	S2	2.195 [55.75]	HBL360RS2W
60	4P5W	600/250	S1	2.50 [63.5]	HBL560RS1W
60	3P4W	600/250	S2	2.50 [63.5]	HBL460RS2W

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
BOX TERMINAL	STEEL	NICKEL PLATE
GROUND STANDOFF	BRASS	
GROUND BRACKET	COPPER ALLOY	NICKEL PLATE
HINGE BUSHING	ALUMINUM	
SPRING GUIDE	STAIN STEEL	
LID SPRING	STAIN STEEL	
LID	ALUMINUM	GRAY EPOXY
LID LIFTER	ALUMINUM	GRAY EPOXY
INTERIOR	THERMOSET POLYESTER	
O-RING	RUBBER	
LID GASKET	RUBBER	
SPRING WASHER	STAIN STEEL	
SCREW - LID	STAIN STEEL	
WAVE SPRING	STAIN STEEL	
RIVET	ALUMINUM	
RECEPTACLE	ALUMINUM	GRAY EPOXY
SCREWS	STAIN STEEL	
PIN SPRING	COPPER ALLOY	SILVER COATED
PINS	BRASS	

3	ADDED TABLE, "SEE TABLE", AND NOTE 1. Ø "A" [A], AND "2X" TO 4.25 [107.95] & 3.50 [88.90]; DRAWING TITLE WAS "60A PIN & SLEEVE RECEPTACLE ASSEMBLY STYLES 1 & 2"; REMOVED "mm" FROM DIMENSIONS; ADDED "COPPER ONLY" TO "WIRE RANGE #6 - #4 AWG"; PER DCN #8685. JMN	TCM	1/21/02
2	DCN 5807-8 2/10/99 UPDATED LIST OF PARTS		
1	RELEASED PER DCN 5641 12/18/97 B.C.	RDK	12/20/97
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE

60A INSULGRIP PIN & SLEEVE
RECEPTACLE
STYLE 1 & 2TOLERANCES UNLESS
OTHERWISE SPECIFIEDFRACTIONS ±1/64
3 DECIMALS ±.005
ANGLES ±2°
2 DECIMALS ±.01WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
BRIDGEPORT, CTDR. BY B.C. APP. BY RDK
TR. BY SCALE 1:1
CHK'D BY RDK DATE 12/18/97