


M-8265 2



NOTES: (UNLESS OTHERWISE SPECIFIED)

1) DIMENSION FORMAT IS: INCHES
[mm]

AMPS	POLES AND WIRES	MAX VOLTAGE AC/DC	STYLE	Ø "A" [A]	CONNECTOR CATALOG NUMBER
60	2P3W	600/250	S1	2.195 [55.75]	HBL360RS1WR
60	3P4W	600/250	S1	2.50 [63.5]	HBL460RS1WR
60	2P3W	600/250	S2	2.195 [55.75]	HBL360RS2WR
60	4P5W	600/250	S1	2.50 [63.5]	HBL560RS1WR
60	3P4W	600/250	S2	2.50 [63.5]	HBL460RS2WR

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
BOX TERMINAL	STEEL	NICKEL PLATE
GROUND STANDOFF	BRASS	
HINGE BUSHING	ALUMINUM	
SPRING GUIDE	STAIN STEEL	
LID SPRING	STAIN STEEL	
LID	ALUMINUM	GRAY EPOXY
LID LIFTER	ALUMINUM	GRAY EPOXY
O-RING	RUBBER	
LID GASKET	RUBBER	
CLAMP NUT	BRASS	NICKEL PLATE
GLAND	RUBBER	
SPRING WASHER	STAIN STEEL	
WAVE SPRING	STAIN STEEL	
RIVET	ALUMINUM	
RECEPTACLE	ALUMINUM	GRAY EPOXY
SCREWS	STAIN STEEL	
SLEEVES	BRASS	
INTERIOR	THERMOSET POLYESTER	
PIN SPRING	COPPER ALLOY	SILVER COATED

2	ADDED TABLE, "SEE TABLE", NOTE 1, Ø "A" [A], AND "2X" TO 4.25 [107.95] & 3.50 [88.90]; DRAWING TITLE WAS "60A PIN & SLEEVE REVERSE RECP. ASSEMBLY STYLES 1 & 2"; REMOVED "MM" FROM DIMENSIONS; ADDED "AWG COPPER ONLY" TO "WIRE RANGE #4 - #6"; PER DCN #8695. JMN	TCM	1/24/02
---	--	-----	---------

1	NEW RELEASE PER DCN 7013 RTK	RDK	8/23/99
---	------------------------------	-----	---------

SYM	REVISIONS	APP	DATE
-----	-----------	-----	------

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE

60A INSULGRIP PIN & SLEEVE REVERSE SERVICE RECEPTACLE STYLE 1 & 2

TOLERANCES UNLESS OTHERWISE SPECIFIED

FRACTIONS ± 1/64
3 DECIMALS ± .005
ANGLES ± 2°
2 DECIMALS ± .01

WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT

DR. BY RTK APP. BY RDK
TR. BY SCALE N/A
CHK'D BY RDK DATE 8/23/99