



REPAIRABLE ☐ NON-REPAIRABLE ☒

B M-6818

1

M-6818 1



NOTE:

- 1.) THIS DEVICE IS NOT WATER TIGHT
- 2.) SHIPPED WITH BODY, CONTACT CARRIER ASSY AND ADAPTER PLATE UNASSEMBLED. ASSEMBLY SCREWS SUPPLIED
- 3.) TERMINAL WIRE CAPACITY - #4 AWG MAX.
- 4.) COLOR RATING AND CONFIGURATION IS COMPATIBLE WITH IEC 309-2
- 5.) APPROVALS - UL LISTED, C.S.A. CERTIFIED.
- 6.) 4-#6 MTG. SCREWS TO MOUNT ADAPTER PLATE TO 2 GANG BOX OR RAISED BOX COVER
4-#8 MTG. SCREWS TO MOUNT ADAPTER PLATE TO 4 11/16 BOX
- 7.) 4-#10 MTG. SCREWS TO MOUNT BODY TO ADAPTER PLATE
- 8.) GREEN PIG TAIL SUPPLIED FOR GROUNDING TO METALIC WIRING SYSTEM

CAT. NO.	RATING	COLOR
A460R9	60A 3Ø 250 VAC	BLUE
A460R12	60A 125/250 VAC	ORANGE
A360R6	60A 250 VAC	BLUE

DO NOT SCALE DWG.

TITLE 60 A PIN & SLEEVE
RECEPTACLE WITH ADAPTER PLATE

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BODY	NYLON	
ADAPTER	ALUMINUM	
CONTACT	BRASS	
CONTACT CARRIER	POLYESTER	
#6 MTG. SCREW	STEEL	ZINC PL.
#8 MTG. SCREW	STEEL	ZINC PL.
#10 MTG. SCREW	STAIN. ST.	
TERMINAL SCREWS	STAIN. ST.	

1	A360R6 ADDED PER DCS 209210 MM	6-24-93
SYM	REVISIONS	APP DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE.

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE DIVISION HARVEY HUBBELL, INC. BRIDGEPORT, CONN.	
FRACTIONS	± 1/64	DR. BY AJL	APP. BY
DECIMALS	± .005	TR. BY	SCALE 3
ANGLES	± 2°	CHK'D. BY	DATE 10-4-89