






1



PANEL CUTOUT
SCALE 2:1



NOTES :

1. DIMENSIONS ARE mm [INCHES].
2. QUICK CONNECT PUSH-IN WIRE TERMINALS FOR 18 AWG SOLID OR TWIST & TIN, STRIPPED 7/16".
MAXIMUM 6.5 LBS. CONDUCTOR INSERTION FORCE.
3. SCREW MOUNT INTO 0.6-1 mm[.025-.040 IN.] PANEL THICKNESS.
EACH WIRING PORT ACCEPTS 2 WIRES FOR EASY HARNESS WIRING,
4. NO EXTRA JUMPERS OR WIRE NUTS TO ASSEMBLE.
5. c UL US LISTED; c CSA US APPROVED.
6. RATED 75W MAX., 600V MAX.
7. PACKAGING: SEALED IN POLYBAG.

CODE 74545

LIST OF PARTS

[illegible]

1	12/01/09 RELEASE TO PRODUCTION PER DCN 16198	CAC CAC	
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
COMPACT FLUORESCENT
LAMPHOLDER, 7/9W G23,
HORZ 2 HOLE SCREW MNT

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS $\pm 1/64$ DECIMALS $\pm .005$ ANGLES $\pm 2^\circ$	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
	DR. BY <u>DLI</u>	APP. BY <u>CAC</u>
	TR. BY	SCALE <u>NONE</u>
	CHK'D BY	DATE <u>04/01/09</u>

DIMENSION SHEET FOR CAT. NO.

R 479HSM

REPAIRABLE ☐

NON-REPAIRABLE ☒



M11278