



M-9924 1



NOTES: (UNLESS OTHERWISE SPECIFIED)

1. FOR USE WITH ALUMINUM AND COPPER WIRE SOLID OR STRANDED.
2. AWG WIRE RANGE: #4-#10
3. DIM'S ARE IN INCHES [MM].
4. (4) MOUNTING SCREWS - NOT SHOWN (SIZE #6-32UNC).

CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
DRIVE SCREW	STEEL	ZINC
WIRE TERMINAL	ALUMINUM	TIN
CONTACT	BRASS	TIN
CONTACT PHASE	BRASS	TIN
RETAINER 4W	PLASTIC	
GROUND CONTACT	BRASS	
HOUSING	PLASTIC	
EYELET	BRASS	ZINC
GROUND SHUNT	BRASS	
TERMINAL SCREW	STEEL	ZINC

REPAIRABLE ☐ NON-REPAIRABLE ☒

1 RELEASE PER DCN# 13450 11/27/08

SYM REVISIONS APP DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
PANEL MOUNT RECEPTACLE
NEMA 14-30R

TOLERANCES UNLESS OTHERWISE SPECIFIED
FRACTIONS ± 1/64
DECIMALS ± .005
ANGLES ± 2°

WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
BRIDGEPORT, CT.

DR. BY MPF APP. BY DMP
TR. BY SCALE 1/1
CHK'D BY DMP DATE 10/3/05