



Power Protection Devices, Receptacle, Self Test, GFCI, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory

By Bryant
Catalog # [GFR20I](#)

Power Protection Devices, Receptacle, Self Test, GFCI, 20A 125V,
2-Pole 3-Wire Grounding, 5-20R, Ivory



Features

- Patented AUTOGUARD® self test technology
- Internal back wiring clamp and guide for quick and secure termination
- Single LED status indicator - green indicates power, red indicates a trip, flashing red indicates end of life

Specifications

Nema Rating	5-20R
Industry Standard(s)	Meets All NEC® Requirements
EU RoHS Indicator	Contact Manufacturer

Current

Voltage Rating Description	125 V
Current / Amperage Rating	20 A

General

Specifications

Color	Ivory
Style	Standard
UPC	883778999109
Type	Standard
Series	Heavy Duty

- Base - Nylon
- Face - Nylon
- Ground Contacts - Brass
- Mounting Screws - Zinc plated steel
- Mounting Strap - Zinc plated steel
- Power Contacts - Brass

Logistics

Pallet Quantity	2240
Carton Quantity	10