

Straight Blade Devices  
 20A, 125V, 2 Pole, 3 Wire Grounding  
 Insulgrip Plug



**Features**

- Ribbed nylon housing is impact and chemical resistant
- VARI-SIZE adjustable cord clamp
- Fast lead assembly screws
- Beveled housing prevents snagging

**Ordering Information**

Description	Cord Diameter	UPC	Catalog Number
Black and white nylon	.230"-.720"(5.8-18.3)	783585173955	HBL5366C



**Listings**

UL Listed to UL498 File E1706  
 CSA Certified to C22.2 No. 42 File 280  
 Fed. Spec. W-C596G  
 NEMA® WD-6 Compliant

**Specifications**

Housing/Cord Clamp	Nylon
Blade Holder	Nylon
Terminal Retainer	Clear Polycarbonate
Blades	.060 in. (1.5) Brass
Terminal Screws	#8-32 Brass , multiple drive
Terminal Clamp	Nickel plated steel
Assembly Screws	Nickel plated steel

**Performance**

**Electrical**



Current Interrupting Certified for current interrupting at full rated current  
 Dielectric Voltage Withstands 2,000V minimum

**Mechanical**

Cord Accomodation .230"-.720"(5.8-18.3)  
 Terminal Accommodation #18-10 AWG. Standed copper wire only  
 Terminal Identification Terminals identified in accordance with UL 498 and CSA

**Environmental**

Flammability UL 94 HB or better  
 IP Suitability IP20  
 Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)



**Accessories**

Weatherproof Boot	HBL6017
-------------------	---------

**Resources**

Customer Use Drawing  
 eCatalog

