

# Twist-Lock® Devices Switched Enclosure Auxillary Contact Auxillary Contact


# HUBBELL

## Ordering Information

Description	Contact Type	UPC	Catalog Number
Auxiliary contact	Break after Break	783585955117	HBLAC1

## Listings

Listed to UL Standard  
Certified to CSA Standard  
Type 3R and 12K Enclosure Rating



## Performance

### Electrical

Current Interrupting Certified for current interrupting at full rated current voltage

Dielectric Voltage Withstands 3,000V Min  
Max. Working Voltage 600V RMS  
Operations Mechanical 10,000 cycles; Electrical 6,000 cycles

### Mechanical

Impact Resistance In accordance with UL 746C  
Mounting External full adjustable feet  
Product Identification Identification and ratings are part of the external label and receptacle face  
Terminal Identification In accordance with UL, CSA

### Environmental

Flammability Meets UL 94V0 material classification  
Moisture Resistance IP66 suitability  
Operating Temperature Maximum continuous +75°C; Minimum continuous -40°C  
UV Resistance All exposed materials are UV stabilized

## Accessories

Enclosure Accommodation Hubbell Non-Fused Switched Enclosures and Non-Fused Mechanical Interlocks with Gray Interior Switches

## Resources

[eCatalog](#)