

**Single Pole Device**  
**RFID Enabled**  
**Series 16**



**Features**

- Industrial Duty, Imbedded RFID tags
- Same electrical and environmental performance as standard Series 16 Single Pole Devices
- Industry best read strength allows for bulk scanning
- Inter-Mateable with any Series 16 style device

**Ordering Information**

Description	Color	Cable Size	UPC Number	Catalog Number
300A, Male Plug	Orange	AWG #6 - 2/0	78358556656	HBLRF300MO

**Listings**

cULus 1691  
 UL94  
 UL Type 4X

**Specifications**

Amperage	300A
Voltage	600V AC/250V DC
Housing Material	Thermoplastic Elastomer (TPE)
Contact Material	Brass
Environmental	UL Type 4X
Weight (lbs)	0.75
RFID Tag Range	Up To 10ft (3m)
Operating Frequency	UHF, Ultra High Frequency
RFID Type	Passive

**Performance**

**Electrical**

Amperage Rating	400A Maximum
Voltage Ratings	600V AC Maximum; 250V DC Maximum

**Mechanical**

Product Identification	Ratings are a permanent part of device
Terminal Accommodation	#6 to 2/0 AWG

**Environmental**

Flammability	HB per UL94 or CSA 22.2. 0.17
--------------	-------------------------------

