

Straight Blade Devices

15A 125V, 2- Pole 3-Wire Grounding

Tamper Resistant Duplex Receptacle

HUBBELL

Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

Ordering Information

Description	Device Color	UPC	Catalog Number
Tamper Resistant- Self Grounding Duplex Receptacle	White	883778301544	RR15SWTR

Listings

UL Listed to UL 498
CSA Certified 22.2, No. 42



Specifications

Face	PVC
Base	PVC
Power Contacts	.030 in. (.8mm) Brass
Ground Contacts	.014 in. (.35mm) Brass
Terminal Screws	Plated Steel
Automatic Self-grounding Staple	Stainless steel
Mounting Screws	Zinc Plated Steel

Performance

Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 1,500V minimum

Mechanical

Terminal	Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only
----------	--

Environmental

Flammability	UL 94 V-2
Operating Temperatures	-20°C to 60°C

Dimensions in Inches (mm)

Specifications subject to change without notice.

