

Wall Plates  
Weatherproof Plates  
Non-Metallic, Extra Duty, Recessed Cover


# HUBBELL

## Features

- NEMA Type 3R, NEC compliant
- Meets extra-duty rating
- Recessed low profile
- Mounts horizontally or vertically

## Ordering Information

Description	Device Color	UPC	Catalog Number
Weatherproof Non-Metallic, Extra Duty, Recessed Cover	Clear/Gray	883778309694	RW5420CG



## Listings


cULus Listed  
UL 94

## Specifications

Cover	Clear Polycarbonate
Base	Polycarbonate
Gasket	Silicon

## Performance

Environmental	
Weatherproof	3R Rated
Flammability	UL V0
Operating Temperatures	Maximum continuous 60°C minimum -40°C (without impact)



Dimensions in Inches (mm)

Specifications subject to change without notice.

