

Ring Terminals



Wire Range	Stud Size		Max. Wire Ins. Dia.		Quantity	Cat. No.	Quantity	Cat. No.
	AWG	mm	In.	mm				
22 – 18 AWG	0,5 – 1,0mm ²	6	3,7mm	0.157	4,0mm	25	—	—
		8	4,3mm			25	—	—
		10	5,3mm			25	—	—
		1/4	6,4mm			25	—	—
16 – 14 AWG	1,5 – 2,5mm ²	6	3,7mm	0.177	4,5mm	25	—	—
		8	4,3mm			25	—	—
		10	5,3mm			25	1,000	84-2241
		1/4	6,4mm			25	—	—
12 – 10 AWG	4,0 – 6,0mm ²	8	4,3mm	0.248	6,3mm	25	—	—
		10	5,3mm			25	1,000	84-2341
		1/4	6,4mm			25	—	—
		5/16	8,4mm			25	—	—
		3/8	10,5mm			25	—	—

75° C/600 Volts max.



Wire Range	Stud Size		Quantity	Cat. No.	Quantity	Cat. No.
	AWG	mm				
22 – 18 AWG	0,5 – 1,0mm ²	8	4,3mm	25	—	—
		10	5,3mm	25	—	—
16 – 14 AWG	1,5 – 2,5mm ²	6	3,7mm	25	—	—
		8	4,3mm	25	—	—
		10	5,3mm	25	1,000	84-0241
12 – 10 AWG	4,0 – 6,0mm ²	8	4,3mm	25	—	—
		10	5,3mm	25	1,000	84-0341
		1/4	6,4mm	25	—	—
8 AWG	8,0mm ²	10	5,3mm	25	500	84-0421
		1/4	6,4mm	25	—	—
		5/16	8,4mm	25	—	—
		3/8	10,5mm	25	—	—
		10	5,3mm	20	—	—
6 AWG	14,0mm ²	1/4	6,4mm	20	—	—
		5/16	8,4mm	20	—	—
		3/8	10,5mm	20	—	—
4 AWG	22,0mm ²	1/4	6,4mm	20	—	—
		5/16	8,4mm	20	—	—
		3/8	10,5mm	20	—	—

105°C/600 Volts max.