

# Spade Terminals



Vinyl Insulated	Wire Range		Stud Size		Max. Wire Ins. Dia.		Quantity	Cat. No.	Quantity	Cat. No.
	AWG	mm	In.	mm	In.	mm				
22 – 18 AWG	0,5 – 1,0mm <sup>2</sup>	6	3,7mm	0.157	4,0mm	25	<b>83-7111</b>	1,000	<b>84-7111</b>	
		8	4,3mm			25	—			
		10	5,3mm			25	—			
16 – 14 AWG	1,5 – 2,5mm <sup>2</sup>	6	3,7mm	0.177	4,5mm	25	<b>83-7151</b>	—	—	
		8	4,3mm			25	<b>83-7161</b>	1,000	<b>84-7161</b>	
		10	5,3mm			25	<b>83-7171</b>	1,000	<b>84-7171</b>	
12 – 10 AWG	4,0 – 6,0mm <sup>2</sup>	6	3,7mm	0.248	6,3mm	25	<b>83-7201</b>	—	—	
		8	4,3mm			25	<b>83-7211</b>	—	—	
		10	5,3mm			25	<b>83-7221</b>	500	<b>84-7221</b>	
		1/4	6,4mm			25	<b>83-7231</b>	—	—	

75° C/600 Volts max.



Vinyl Insulated Snap	Wire Range		Stud Size		Max. Wire Ins. Dia.		Quantity	Cat. No.
	AWG	mm	In.	mm	In.	mm		
22 – 18 AWG	0,5 – 1,0mm <sup>2</sup>	6	3,7mm	0.134	4,0mm	25	<b>83-7011</b>	
		8	4,3mm			25	<b>83-7021</b>	
		10	5,3mm			25	<b>83-7031</b>	
16 – 14 AWG	1,5 – 2,5mm <sup>2</sup>	6	3,7mm	0.161	4,5mm	25	<b>83-7051</b>	
		8	4,3mm			25	<b>83-7061</b>	
		10	5,3mm			25	<b>83-7071</b>	
12 – 10 AWG	4,0 – 6,0mm <sup>2</sup>	8	4,3mm	0.248	6,mm	25	<b>83-7081</b>	
		10	5,3mm			25	<b>83-7091</b>	
		1/4	6,4mm			25	<b>83-7101</b>	

75° C/600 Volts max.

