






## Replacement Tips (for Twist-a-Nut™ and Ratch-a-Nut™ Screwdrivers)

| Description                    |   | Cat. No. |
|--------------------------------|---|----------|
| 1/4 in. slotted – #2 Phillips  |  | 35-911   |
| 3/16 in. slotted – #1 Phillips |  | 35-912   |
| 1/4 in. slotted – #2 Square    |  | 35-913   |
| 3/16 in. slotted – #1 Square   |  | 35-914   |
| #15 & #10 Star                 |  | 35-915   |

## 6-in-1 Twist-a-Nut™ Tap Tool

- Forms new threads, re-forms burred threads and cleans out obstructions
- Reversible, high-carbon tap with three clearly marked thread sizes on each end
- Handle is interchangeable with 7-in-1 Screwdriver (#35-908) and Conduit Deburrer (#35-083)
- Includes: 6-32, 8-32 & 10-32 on one tapping side and 10-24, 12-24 & 1/4-20 on other side



(Lifetime warranty excludes taps)

| Description                     |   | Cat. No. |
|---------------------------------|---|----------|
| Twist-a-Nut™ Tapping Tool       |   | 35-922   |
| Replacement collar and six taps |  | 35-923   |

## Twist-a-Nut™ Conduit Deburring Tools

- Deburrs inside and outside edges of 1/2 in., 3/4 in. and 1 in. thin wall conduit
- Hooded tip tightens EMT fitting set screws without slipping
- Square tip “seats” much more quickly on fitting screws than slotted version
- Head removes and is interchangeable with IDEAL 7-in-1 Twist-a-Nut™ Screwdriver shaft (#35-908)
- Head can be used at low speed setting in drill or cordless screwdriver



(Lifetime warranty excludes bits & blades)

| Description                        | Tip Type  | Cat. No. |
|------------------------------------|-----------|----------|
| Conduit Deburring Tool             | Slotted   | 35-083   |
| Conduit Deburring Tool             | #2 Square | 35-075   |
| Conduit Deburring Tool (head only) | Slotted   | 35-096   |
| Conduit Deburring Tool (head only) | #2 Square | 35-098   |