

## Heavy-Duty Round Shaft Keystone Cushioned-Grip Screwdrivers



- Larger shank for heavy-duty applications

Round Shank	Blade Length	Handle Length	Overall Length	Cat. No.
1/4 in. shank and tip	1-1/2 in.	1-15/16 in.	3-7/16 in.	<b>35-161</b>
1/4 in. shank and tip	4 in.	4-5/16 in.	8-5/16 in.	<b>35-164</b>
5/16 in. shank and tip	6 in.	5-11/32 in.	11-11/32 in.	<b>35-166</b>
3/8 in. shank and tip	8 in.	5-11/32 in.	13-11/32 in.	<b>35-168</b>

## Heavy-Duty Square Shaft Keystone Cushioned-Grip Screwdrivers



- Larger shank for heavy-duty applications
- Square-shank models offer wrench-assisted turning

Square Shank	Blade Length	Handle Length	Overall Length	Cat. No.
1/4 in. shank and tip	4 in.	4-5/16 in.	8-5/16 in.	<b>35-154</b>
5/16 in. shank and tip	6 in.	5-11/32 in.	11-11/32 in.	<b>35-156</b>
3/8 in. shank and tip	8 in.	5-11/32 in.	13-11/32 in.	<b>35-158</b>

## Combo Head™ Cushioned-Grip Screwdriver



- Designed to accurately and securely fit most Combination Fasteners
- Patented design

Description	Blade Length	Handle Length	Overall Length	Cat. No.
Combo Head™ Cushioned-Grip Screwdriver	4 in.	4-5/16 in.	8-5/16 in.	<b>35-204</b>

## Quick Rotating Screwdriver

- Ideal for threading screws in switches, fixtures and anchors
- One-handed crank action for quick and easy use



Description	Blade Length	Handle Length	Overall Length	Cat. No.
Cabinet Quick Rotating Screwdriver	5-9/16 in.	3-3/4 in.	9-3/8 in.	<b>35-200</b>
Phillips Quick Rotating Screwdriver	5-5/8 in.	4-5/16 in.	9-15/16 in.	<b>35-203</b>

## Awl

- Heavy-duty construction for piercing, punching and scribing



Description	Blade Length	Handle Length	Overall Length	Cat. No.
Awl	3 in.	3-3/4 in.	6-3/4 in.	<b>35-202</b>