

Ultrasonic Sensors	
US18-PA-5-N03-IH Ultrasonic M18 axial - 4-20 mA analogue - M12	95B040020
US18-PA-5-N03-OH Ultrasonic M18 axial - PNP/NPN- M12	95B040000
US18-PA-5-N03-VH Ultrasonic M18 axial - 0-10V analogue - M12	95B040040
US18-PL-5-N03-NH Ultrasonic square right angle mounting - NPN - M12	95B040140
US18-PL-5-N03-PH Ultrasonic square right angle mounting - PNP - M12	95B040150
US18-PR-5-N03-IH Ultrasonic M18 radial - 4-20 mA analogue - M12	95B040030
US18-PR-5-N03-OH Ultrasonic M18 radial - PNP/NPN- M12	95B040010
US18-PR-5-N03-VH Ultrasonic M18 radial - 0-10V analogue - M12	95B040050
US30-PR-5-N13-IH Ultrasonic M30 radial 1000 mm - 4-20 mA analogue - M12	95B040060
US30-PR-5-N13-OH Ultrasonic M30 radial 1000 mm- PNP/NPN- M12	95B040100
US30-PR-5-N13-VH Ultrasonic M30 radial 1000 mm - 0-10V analogue - M12	95B040070
US30-PR-5-N23-IH Ultrasonic M30 radial 2000 mm - 4-20 mA analogue - M12	95B040080
US30-PR-5-N23-OH Ultrasonic M30 radial 2000 mm- PNP/NPN- M12	95B040110
US30-PR-5-N23-VH Ultrasonic M30 radial 2000 mm - 0-10V analogue - M12	95B040090
US50-PR-5-N43-IVH Ultrasonic radial 8000 mm - analogue output - M12	95B040130
US50-PR-5-N43-OH Ultrasonic radial 8000 mm - PNP/NPN - M13	95B040120

CABLES	
Cable M12 4-p axial 10m	95A251390
Cable M12 4-p axial 10m CEI 2034-01	95A251090
Cable M12 4-p axial 10m UL 2464	95ASE1140
Cable M12 4-p axial 15m UL 2464	95ASE1150
Cable M12 4-p axial 25m UL 2464	95ASE1160
Cable M12 4-p axial 3m	95A251380
Cable M12 4-p axial 3m UL 2464	95ASE1120
Cable M12 4-p axial 5m	95A251270
Cable M12 4-p axial 5m CEI 2034-01	95A251710

Cable M12 4-p axial 5m PUR	95A251560
Cable M12 4-p axial 5m UL 2464	95ASE1130
Cable M12 4-p axial PG	G5085002
Cable M12 4-p radial 10m	95A251260
Cable M12 4-p radial 10m CEI 2034-01	95A251700
Cable M12 4-p radial 10m LED	95A251370
Cable M12 4-p radial 2m PUR	95A251550
Cable M12 4-p radial 3m	95A251360
Cable M12 4-p radial 3m LED	95A251400
Cable M12 4-p radial 5m	95A251240
Cable M12 4-p radial 5m CEI 2034-01	95A251690
Cable M12 4-p radial 5m LED	95A251350
Cable M12 4-p radial 5m PUR	95A251570
Cable M12 4-p radial PG	G5085003
Cable M12 5-p axial 10m	95ACC2140
Cable M12 5-p axial 10m UL 2464	95ASE1190
Cable M12 5-p axial 15m UL 2464	95ASE1200
Cable M12 5-p axial 25m UL 2464	95ASE1210
Cable M12 5-p axial 3m	95ACC2110
Cable M12 5-p axial 3m UL 2464	95ASE1170
Cable M12 5-p axial 50m UL 2464	95A252700
Cable M12 5-p axial 5m	95ACC2120
Cable M12 5-p axial 5m UL 2464	95ASE1180

MOUNTS/STANDS	
S67Y MOUNTING KIT	95ACC8160
SP-40 Tubular mounting bracket	95ACC1370
ST1218 M12/M18 mounting brackets	95ACC3340
ST1830 M18/M30 mounting brackets	95ACC3350
ST-30MM Stainless steel bracket for US50	95ACC7830
ST-30SC Assial bracket for US50	95ACC7820
ST-5011 M18 mounting bracket short	95ACC5240
ST-5012 M18 mounting bracket long	95ACC5250
ST-5017 M18 mounting bracket	95ACC5270