



# Industrial Control & Automation Catalog - U908 Master Price List

*Terms & Conditions*

*Table of Contents*

*Master Price List*

*Approvals & Standards*

*Mature Product List*

for the most current and up-to-date information visit

**[www.idec.com](http://www.idec.com)**

This Master Price List (MPL) replaces and  
supersedes all previous versions. The  
effective date of this MPL is Sept. 1, 2005.

Catalog Number **MPLCAT-CD U908-0** 02/06

## Standard Distributor Terms and Conditions

### 1. Responsibility And Title:

All orders are acknowledged, either in writing or by actual shipment, after final acceptance by IDEC. Title to merchandise remains with IDEC as security until full payment has been made. Risk of loss shall pass to Buyer upon delivery to carrier at IDEC's FOB point.

### 2. Shipments:

Refer to IDEC Distributor Shipping and Handling Policy (SHP-02).

### 3. Delivery Schedule:

IDEC shall not be liable for delays in delivery or failure to perform due to causes beyond reasonable control of IDEC. IDEC reserves the right to bill for merchandise and charges for warehousing, insurance, trucking and other associated expenses, if and when shipment should be held beyond scheduled date at the request of Buyer.

### 4. Cancellations:

No order accepted by IDEC may be altered or modified by Buyer unless agreed to in writing signed by an authorized official of IDEC, and no such order may be canceled or terminated except upon payment of IDEC's loss, damage and expense arising from such cancellation or termination.

### 5. Special Handling:

If special transportation, packaging or overseas shipment is requested by Buyer, IDEC reserves the right to assess special handling charges.

### 6. Terms of Payment:

One percent (1%) discount if paid within ten (10) days from date of invoice, or total amount of invoice within thirty (30) days. Past due accounts are subject to a finance charge of 1.5% per month (annual percentage 18%) or the maximum rate permitted by law, whichever is less.

### 7. Inspection and Acceptance of Merchandise:

Buyer is responsible for evaluating received merchandise for final acceptance. All claims for shortages must be made within thirty (30) days from receipt of merchandise.

### 8. Returns:

No merchandise shall be returned unless return authorization has been secured from IDEC. All returns must comply with IDEC Returned Goods Policy (RGP-02).

### 9. Warranty:

IDEC warrants its merchandise to be free from defects in material and workmanship under normal and proper use for a period of one (1) year from date of shipment. IDEC will supply Buyer, IDEC FOB point, replacement merchandise on parts found to be defective upon IDEC's inspection. This warranty is in lieu of all other warranties whether expressed, implied or statutory, including implied warranties of merchantability and of fitness. IDEC shall not be liable for claims based on breach of warranty or negligence or any other damages including consequential, contingent or incidental damages. Warranty does not apply if the merchandise is altered or modified in any way after delivery by IDEC.

### 10. Patents:

IDEC shall have no liability of any kind with respect to any actual or alleged infringement of any United States or foreign patent, trade mark or similar rights.

### 11. Technical Data:

Buyer shall not use, duplicate or disclose any technical data delivered or disclosed by IDEC to Buyer for any purpose other than for use, operation or maintenance of merchandise purchased by Buyer, without IDEC's prior written consent.

### 12. Taxes:

Unless Buyer provides IDEC with tax exemption certificates acceptable to the taxing authorities, Buyer shall pay any sales, use, excise or similar tax attributable to the sale of merchandise covered hereby.

### 13. Governing Law:

This agreement and performance by the parties hereunder shall be constructed in accordance with the law of the state of California.

### 14. Specifications, Dimensions & Pricing:

Subject to change without notice.

© 2005 IDEC Corporation. All rights reserved.

1175 Elko Drive

Sunnyvale, CA 94089-2209, USA

Tel (408) 747-0550

Toll Free (800) 262-IDEC

Fax (408) 744-9055

Toll Free Fax (800) 635-6246

For product questions please email [support@idec.com](mailto:support@idec.com). For ordering or other information, please contact customer service at [csr@idec.com](mailto:csr@idec.com), visit our web site or call us at 800-262-IDEC.

Catalog Number **MPLCAT-CD U908-0** 09/05

Part Number	Description	Discount Code		List Price
AW-G4	AW-G4 TW MSHRM FULL SHROUD	50	0	\$21.00
AW-H1B	AW-H1B TW SQ BEZEL W/RND HOLE	50	0	\$6.00
AW-H1Y	AW-H1Y TW SQ BEZEL W/RND HOLE	50	0	\$6.00
AW-Q0	AW-Q0 ROUND RING FOR AWQ1B	50	0	\$0.50
AW-Q12B	AW-Q12B SQ.RETAINER FOR AWQ1B	50	0	\$0.50
AW-Q1B	AW-Q1B TW PLASTIC SQ BEZEL	50	0	\$6.00
AW-QF1B	AW-QF1B TW EXT SQ BEZEL (1 pc)	50	0	\$6.25
AW-R1	AW-R1 22MM ROUND LOCKING RING	50	0	\$3.00
AW-R1B	AW-R1B TW 22MM ALUMINUM BLACK ROUND FLUSH LOCKING RING	50	0	\$3.00
AW-R8	AW-R8 TW CHROME OCTAL BEZEL	50	0	\$3.00
AW-RF8	AW-RF8 TW CHRME EX OCTAL BEZEL	50	0	\$9.00
AW-RP1B	AW-RP1B TW BLK PLSTC LOCK RING	50	0	\$4.00
AXW-300	AXW-300 TW PUSH LK KEY OPER SW	50	0	\$51.75
AXW-300FN	AXW-300FN	50	0	\$51.95
AXW-300-KEY#1	AXW-300-KEY#1 TW PSH LK KEY SW	50	6	\$51.75
AXW-300-KEY#2	AXW-300-KEY#2 TW PSH LK KEY SW	50	6	\$51.75
AXW-300-KEY#3	AXW-300-KEY#3 TW PSH LK KEY SW	50	6	\$51.75
AXW-300-W/AW-R1	AXW-300-W/AW-R1 TW PSH LK KEY SW	50	0	\$51.75
AXW301-R	AXW301-R TW PSH LK KEY OPER SW	50	6	\$65.85
AXW3B-R	AXW3B-R TW 30MM PSH LK KEY BTN	50	0	\$6.00
AXW401-R	AXW401-R TW PSH LK KEY OPER SW	50	6	\$65.85
AXW402-R	AXW402-R TW PSH LK KEY OPER SW	50	6	\$73.95
AXW410-R	AXW410-R TW PSH LK KEY OEPR SW	50	6	\$65.85
AXW411-R	AXW411-R TW PSH LK KEY OPER SW	50	6	\$73.95
AXW413-R	TW Estop Psh Lck-Key Rst 1NO/3NC 40mm Mshrm	50	6	\$90.15
AXW420-R	AXW420-R TW PSH LK KEY OPER SW	50	6	\$73.95
AXW422-R	AXW422-R TW PSH LK KEY OPER SW	50	6	\$89.85
AXW4B-R	AXW4B-R TW 40MM PSH LK KEY BTN	50	0	\$6.00
AXWN-300	AXWN-300 TWN PUSH-LOCK OPER SW	50	4	\$52.31
AXWN-402-R	AXWN-402-R TWN PUSH-LOCK SW	50	4	\$87.65
AYD301N-B	AYD301N-B TWTD PUSH-PULL PB	50	7	\$61.20
AYD301N-G	AYD301N-G TWTD PUSH-PULL PB	50	7	\$61.20
AYD301N-R	AYD301N-R TWTD PUSH-PULL PB	50	7	\$61.20
AYD301N-S	AYD301N-S TWTD PUSH-PULL PB	50	7	\$61.20
AYD301N-Y	AYD301N-Y TWTD PUSH-PULL PB	50	7	\$61.20
AYD301SN-R	AYD301SN-R TWTD PUSH-PULL PB	50	7	\$61.20
AYD302N-B	AYD302N-B TWTD PUSH-PULL PB	50	7	\$70.20
AYD302N-G	AYD302N-G TWTD PUSH-PULL PB	50	7	\$70.20
AYD302N-R	AYD302N-R TWTD PUSH-PULL PB	50	7	\$70.20
AYD302N-S	AYD302N-S TWTD PUSH-PULL PB	50	7	\$70.20
AYD302N-Y	AYD302N-Y TWTD PUSH-PULL PB	50	7	\$70.20
AYD302SN-R	AYD302SN-R TWTD Push-Pull PB	50	7	\$70.00
AYD303N-R	AYD303N-R TWTD PUSH-PULL PB	50	7	\$79.20
AYD3103-R	AYD3103-R TWTD PUSH/PULL	50	7	\$79.60
AYD310N-B	AYD310N-B TWTD PUSH-PULL PB	50	7	\$61.20
AYD310N-G	AYD310N-G TWTD PUSH-PULL PB	50	7	\$61.20
AYD310N-R	AYD310N-R TWTD PUSH-PULL PB	50	7	\$61.20
AYD310N-S	AYD310N-S TWTD PUSH-PULL PB	50	7	\$61.20
AYD310N-Y	AYD310N-Y TWTD PUSH-PULL PB	50	7	\$61.20
AYD311N-B	AYD311N-B TWTD PUSH-PULL PB	50	7	\$70.20
AYD311N-G	AYD311N-G TWTD PUSH-PULL PB	50	7	\$70.20